

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

C

B



A

D




C

B

A



- 1 GLASS FILLED THERMOPLASTIC, UL 94-V0 RATED, COLOR:BLACK
- 2 PART NO. AND DATE CODE MARKED IN APPROX. AREA SHOWN WHEN HOUSING SIZE PERMITS.
- 3 CAVITY IDENTS, MARKED FIRST AND EVERY FIFTH CAVITY (ONE SIDE) AS SHOWN
- 4 TOLERANCE NON-CUMULATIVE.
- 5. USE EXTRACTION TOOL 91052-1 TO REMOVE RECEPTACLE CONTACTS.
- 6 TE LOGO MOLDED IN TEXTURED AREA AS SHOWN.
- 7 FLASH ALLOWED TO BE 0.38 IN THIS AREA.
- 8 OBOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SCALE 2:1

SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. BRANDBERG CHK S. SHUEY APVD D. DUPLER	21-JUN-95 21-JUN-95 21-JUN-95	TE Connectivity		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME HOUSING, MOD IV, SINGLE ROW, .100 CL, CRIMP SNAP-IN		SIZE	CAGE CODE	DRAWING NO
	0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -	PRODUCT SPEC APPLICATION SPEC WEIGHT		A2	00779	C-87499
MATERIAL - 1	-	CUSTOMER DRAWING		SCALE 4:1	SHEET 2 OF 2	REV. W2