


P	LTR	DESCRIPTION	DATE	DWN	APVD
	AI	NEW DRAWING	08MAR2024	AN	VN



PRODUCT DIMENSIONS

SIZES	AS SUPPLIED		AS RECOVERED			
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		WALL THICKNESS AFTER RECOVERY (W)	
	mm.	in.	mm.	in.	mm.	in.
3/1.5	3.00	0.118	1.50	0.059	0.50±0.10	0.020±0.004
6/3	6.00	0.236	3.00	0.118	0.60±0.10	0.024±0.004
8/4	8.00	0.315	4.00	0.157	0.65±0.10	0.026±0.004
10/5	10.00	0.394	5.00	0.197	0.65±0.10	0.026±0.004
12/6	12.00	0.472	6.00	0.236	0.65±0.10	0.026±0.004
19/9	19.00	0.748	9.00	0.354	0.75±0.15	0.030±0.006
26/13	26.00	1.024	13.00	0.512	0.90±0.15	0.035±0.006
38/19	38.00	1.496	19.00	0.748	1.00±0.15	0.039±0.006


PRODUCT INFORMATION

- 1 FLAME RETARDANT
- 2 MATERIAL: IRRADIATED MODIFIED POLYOLEFIN
STANDARD COLOUR: YELLOW/GREEN STRIPE
- 3 SHRINK RATIO 2:1
- 4 LONGITUDINAL CHANGE 0 TO -10%
- 5 TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.1
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±
FINISH -

DWN	08MAR2024
AYESHABANU N	
CHK	08MAR2024
BASAVARAJA D A	
APVD	08MAR2024
VLADIMIR NEMEC	
PRODUCT SPEC	RW-2056
APPLICATION SPEC	114-120022
WEIGHT	-
CUSTOMER DRAWING	



NAME
DCPT (2:1 RATIO) (YELLOW/GREEN STRIPED)
- IRRADIATED MODIFIED POLYOLEFIN
SINGLE WALL HEAT SHRINK TUBING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	DCPT.2_TO.1_STANDARD_SIZES	-

SCALE NTS SHEET 1 OF 1 REV AI