

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	PLATING CHANGED TO TRIBOR	10JAN2017	RP	PS

NUMMER 966443

VERWENDET FÜR


ALL RIGHTS RESERVED.

RELEASED FOR PUBLICATION  
FREI FÜR VERÖFFENTLICHUNG

THIS DRAWING IS UNPUBLISHED.  
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG.

© COPYRIGHT - By -

POS.	L±0.4	PART NUMBER
2	5.08	
3	7.62	
4	10.16	5-966443-4
5	12.70	
6	15.24	5-966443-6
7	17.78	
8	20.32	
9	22.86	
10	25.40	6-966443-0
11	27.94	
12	30.48	
13	33.02	
14	35.56	
15	38.10	
16	40.64	
17	43.18	
18	45.72	
19	48.26	
20	50.80	
21	53.34	
22	55.88	
23	58.42	
24	60.96	
25	63.50	
26	66.04	
27	68.58	
28	71.12	
29	73.66	
30	76.20	
31	78.74	
32	81.28	
33	83.82	
34	86.36	
35	88.90	
36	91.44	
37	93.98	
38	96.52	
39	99.06	
40	101.60	
41	104.14	
42	106.68	
43	109.22	
44	111.76	
45	114.30	
46	116.84	
47	119.38	
48	121.92	
49	124.46	
50	127.00	9-966443-9



2	CONTACT PIN	CuSn	△
1	PIN HOUSING	PBT	GREEN
ITEM	DESCRIPTION	MATERIAL	SURFACE/COLOUR

REMARKS:

△ FINISH: TRIBOR®  
 UNDERLAYER: 2-4µm Ni-P(NICKEL-PHOSPHOROUS)  
 CONTACT AREA: 0.12-0.27µm Au(GOLD) BY AREA "F"  
 SOLDER TYNES: 3-5µm Sn(MATTE TIN)

2. PERMEABILITY  $\mu_R \leq 1.0005$

DIMENSIONS: mm	DWN F.RIECHARDT 17.02.94	MATERIAL -	FINISH OBERFLAECHE/FARBE -
	CHK M.SCHAARSCHMIDT 17.02.94	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN ± 0.2mm	APVD -		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES / WINKEL ± -	PRODUCT SPEC PRODUKTSPEZ. -	SIZE A4	CAGE CODE 00779
	APPLICATION SPEC -	DRAWING NO C-966443	RESTRICTED TO -
	WEIGHT GEWICHT	SCALE 1:1	
CUSTOMER DRAWING		SHEET BLATT 1	REV B