


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL CREATION	09MAR2022	SM	JG
	A1	REVISED PER RTS# 1658263	21APR2022	BN	JG



6 SHAPE GROUNDING CONNECTORS									
Catalog No.	Part No.	AWG Copper Cable Range		Metric Copper Cable Range		Cable To Rebar		Height (A)	Width (B)
		Run (AWG)	Tap (AWG)	Run (Sq.mm.)	Tap (Sq.mm.)	Run	Tap (AWG)	Inch (mm)	Inch (mm)
TCC6 29-2	EN3751-091	1/0 STR - 250 MCM 1/2" - 5/8" Rod	#4 SOL - #2 STR	50 - 120 (12.7mm or 15.9mm Rod)	25 - 35	#3 Rebar 3/8, 1/2 #4 Rebar	#2 STR	2.10 (53.3)	0.75 (19.0)
TCC6 29-26	EN3751-143	1/0 STR - 250 MCM 1/2" - 5/8" Rod	1/0 STR - 2/0 STR	50 - 120 (12.7mm or 15.9mm Rod)	50 - 70	#3 Rebar 3/8, 1/2 #4 Rebar	1/0 STR - 2/0 STR	2.10 (53.3)	0.75 (19.0)
TCC6 29-29	EN3751-144	1/0 STR - 250 MCM 1/2" - 5/8" Rod	3/0 STR - 250 MCM	50 - 120 (12.7mm or 15.9mm Rod)	95 - 120	#3 Rebar 3/8, 1/2 #4 Rebar	3/0 STR - 250 MCM	2.10 (53.3)	0.75 (19.0)
TCC6 34-2	EN3751-284	250 MCM - 500 MCM 5/8" - 3/4" Rod	#4 SOL - #2 STR	120 - 240 (15.9mm or 19.0mm Rod)	25 - 35	#5 Rebar 5/8, 3/4 #6 Rebar	-	2.58 (65.5)	0.75 (19.0)
TCC6 34-26	EN3751-285	250 MCM - 500 MCM 5/8" - 3/4" Rod	1/0 STR - 2/0 STR	120 - 240 (15.9mm or 19.0mm Rod)	50 - 70	#5 Rebar 5/8, 3/4 #6 Rebar	1/0 STR - 2/0 STR	2.58 (65.5)	0.75 (19.0)
TCC6 34-29	EN3751-286	250 MCM - 500 MCM 5/8" - 3/4" Rod	3/0 STR - 250 MCM	120 - 240 (15.9mm or 19.0mm Rod)	95 - 120	#5 Rebar 5/8, 3/4 #6 Rebar	3/0 STR - 250 MCM	2.58 (65.5)	0.75 (19.0)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCH [mm]

DWNTOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —

MATERIAL
ETP—COPPER

FINISH
—

DWNTCHKAPVDPRODUCT SPECAPPLICATION SPECWEIGHT

M. SATYAJ. GUPPYJ. OPEL—
09MAR202209MAR202209MAR2022

NAME

SIZECAGE CODEDRAWING NORESTRICTED TO

A300779C—E00001690—

CUSTOMER DRAWING

SCALENTS

SHEET1 OF 1

REVA1

TE Connectivity

6 SHAPE GROUNDING CONNECTORS

1470—19 (1/15)