




DEADEND

**CATALOGUE NUMBER: FAD1080-1130-6
SUITS CONDUCTOR**

STRANDING/CONDUCTOR	COND. TYPE	DIAMETER	FITTING LAY
7/3.75	AAC/AAAC	11.25	RIGHT HAND
7/0.144	AAC/AAAC	10.97	RIGHT HAND



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FAD1080-1130-6
 DESCRIPTION: FULL-TENSION ALUMINIUM DEADEND
 MATERIAL: ALUMINIUM ALLOY
 NUMBER OF RODS: 6
 ROD DIAMETER: 2.95mm
 OVERAL LENGTH: 680mm
 END FINISH: CHAMFERED
 FITTING LAY DIRECTION: RIGHT HAND
 COLOUR CODED: BLACK

PRODUCT LABEL

FAD1080-1130-6
 7/3.75 AAC/AAAC
 7/0.144 AAC/AAAC

WEIGHT: 0.17kg
 BATCH NO:
 MONTH/YEAR:

BOX LABEL

P/N: FAD1080-1130-6
 ID:
 DESCRIPTION:
FULL-TENSION ALUMINIUM DEADEND
 7/3.75 AAC/AAAC
 7/0.144 AAC/AAAC
 RANGE: 10.80 - 11.30
 COLOUR-CODE: **BLACK**
 QTY: 25 WEIGHT: BATCH:

LOC							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5%. UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°	TCPN - PART Alias UTX/DUL FAD1080-1130-6 Cat No FAD1080-1130-6	TITLE FULL-TENSION ALUMINIUM DEADEND (FAD) FITTING COND. RANGE: Ø10.80-Ø11.30 7/3.75 AAC/AAAC 7/0.144 AAC/AAAC	DRAWN RN	DATE 16-05-2013		TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia		
DIST	—	I	NEW RELEASE	16-05-2013	RN	AT	MATERIAL DESC ALUMINIUM ALLOY	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO	SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO FAD1080-1130-6-C	SHEET OF 1 1	REV 1
POS	REV	REVISION RECORD			DATE	DWN	APVD				Format: generic_m03.au.r1.fm 4	Template: tec_generic_a3_metric.au.r1.dwg 3	Dwg No from P1 Mod Fam Tbl: 2 >AUXXXXX			

D
C
B
A