


REVISIONS				
P	LR	DESCRIPTION	DATE	BY
A2		INITIAL RELEASE	14MAR2023	MIN AK

4

3

2

1



All dimensions in mm [Inches]

TE PN: 9-1768016-9  
 LABEL ACROSS: 6  
 PER SHEET QTY: 120

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [0.02]
LABEL WIDTH:	±0.3 [0.02]
MED WIDTH:	±0.8 [0.03]
VERTICAL REPEAT:	±0.8 [0.03]*
HORIZONTAL REPEAT:	±0.8 [0.03]*
FRONT POSITIONING:	±0.8 [0.03]*
LEFT MARGIN:	±0.4 [0.06]
QUANTITY:	-0% +2%
*NON ACCUMULATING	

DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PIC	±	1 PIC	±
2 PIC	±	3 PIC	±
4 PIC	±	FINISH	±

THIS DRAWING IS A CONTROLLED DOCUMENT.		MATERIAL	
DM	M. NUTTALL	14MAR2023	YELLOW NYLON FABRIC
CHK	M. NUTTALL	14MAR2023	ADHESIVE TYPE
APVD	A. KEAN	14MAR2023	PERMANENT ACRYLIC
PRODUCT SPEC	TTDS-181		GLASSINE PAPER
APPLICATION SPEC			
WEIGHT	0.040 g	SIZE	A2
CUSTOMER DRAWING		QAGE CODE	A00YM
		DRAWING NO	9-1768016-9
		SCALE	NTS
		SHEET	1 of 1
		REV	A2