


DRAWING NO: FCD1320-1375-6-C
THIS DRAWING IS A CONTROLLED DOCUMENT



CATALOGUE NUMBER: FCD1320-1375-6 SUITS CONDUCTOR

DEADEND


| STRANDING | COND. TYPE | DIAMETER | FITTING LAY |
|-----------|------------|----------|-------------|
| 19/2.75 | COPPER | 13.75 | RIGHT HAND |
| 19/0.104 | COPPER | 13.21 | RIGHT HAND |




TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FCD1320-1375-6
 DESCRIPTION: FULL-TENSION HARD DRAWN COPPER DEADEND
 MATERIAL: HARD DRAWN COPPER WIRE
 NUMBER OF RODS: 6
 ROD DIAMETER: 3.65mm
 OVERAL LENGTH: 910mm
 END FINISH: CHAMFERED
 FITTING LAY DIRECTION: RIGHT HAND
 COLOUR CODED: WHITE

PRODUCT LABEL



BOX LABEL



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.

| | | | | | | | | | | | | | | | |
|------|-----|-----------------|-------------|------------|-----|------|---|--|---|---|---|--------------|--------------------------------|--|----------|
| LOC | | | | | | | IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE | IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5% UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5° | TCPN - | PART Alias UTX/DUL FCD1320-1375-6 | TITLE FULL-TENSION HARD DRAWN COPPER DEADEND (FCD) FITTING COND. RANGE: Ø13.20-Ø13.75 19/2.75 COPPER 19/0.104 COPPER | | | | |
| DIST | — | I | NEW RELEASE | 16-05-2013 | RN | AT | MATERIAL DESC HARD DRAWN COPPER WIRE | MATERIAL NO - | MATL SPEC/STD/DRG NO - | PROCESS SPEC HEAT TREAT/PLATING NO - | Cat No FCD1320-1375-6 | DRAWN RN | DATE 16-05-2013 | TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia | |
| POS | REV | REVISION RECORD | | DATE | DWN | APVD | MATERIAL NO - | MATL SPEC/STD/DRG NO - | PROCESS SPEC HEAT TREAT/PLATING NO - | SIZE A3 | PROJECTION 3RD ANGLE | SCALE NTS | DRAWING NO FCD1320-1375-6-C | SHEET OF 1 1 | REV 1 |

Format: generic_m03.au.r1.fm 4

Template: tec_generic_a3_metric.au.r1.drw 3

Dwg No from P1 Mod Fam Tbl: 2 >AUXXXXX