




CATALOGUE NUMBER: FCD1810-1900-6 SUITS CONDUCTOR

DEADEND

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
37/0.103	COPPER	18.31	RIGHT HAND
19/0.149	COPPER	18.92	RIGHT HAND



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FCD1810-1900-6
DESCRIPTION: FULL-TENSION HARD DRAWN COPPER DEADEND
MATERIAL: HARD DRAWN COPPER WIRE
NUMBER OF RODS: 6
ROD DIAMETER: 4.47mm
OVERAL LENGTH: 1235mm
END FINISH: BALLENDDED
FITTING LAY DIRECTION: RIGHT HAND
COLOUR CODED: WHITE

PRODUCT LABEL

FCD1810-1900-6
 37/0.103 COPPER
 19/0.149 COPPER

WEIGHT: 2.24kg
BATCH NO:
MONTH/YEAR:

BOX LABEL

P/N: FCD1810-1900-6
ID:
DESCRIPTION:
FULL-TENSION COPPER DEADEND
37/0.103 COPPER
19/0.149 COPPER
RANGE: 18.10 - 19.00
COLOUR-CODE: WHITE
QTY: 5 **WEIGHT:** **BATCH:**

LOC							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5% UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°	TCPN - PART Alias UTX/DUL FCD1810-1900-6 Cat No FCD1810-1900-6	TITLE FULL-TENSION HARD DRAWN COPPER DEADEND (FCD) FITTING COND. RANGE: Ø18.10-Ø19.00 37/0.103 COPPER 19/0.149 COPPER	DRAWN RN CHECKED MN	DATE 20-05-2013 APPROVED AT	TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia				
DIST	—	I	NEW RELEASE	20-05-2013	RN	AT	MATERIAL DESC HARD DRAWN COPPER WIRE	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO -	SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO FCD1810-1900-6-C	SHEET 1	OF 1	REV 1
POS	REV	REVISION RECORD			DATE	DWN	APVD										