


Recommended torque:
23 Newton meters

POS-NR.	DESCRIPTION	QUANTITY
1	Frame, steel hot dipped	1
2	Upper part, brass tin-plated	1
3	Screw, brass tin-plated	1
4	Tension washer, spring steel	1
5	Pressure plate	1
6	Contact part, brass tin-plated	1

Burr Projection:		Debur and Break Sharp Edges		DO NOT SCALE DRAWING		Revision: 1	
Form Bound Measure:		Dimension: mm		This information is confidential and proprietary to Tyco Electronics Corporation and its subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronics personnel, without written authorization from Tyco Electronics Corporation, Harrisburg, Pennsylvania USA.			
Not Form Bound Measure:		Description: Steel type flat direct terminal clamp HEL-4865; RPN: 251934-000 for single conductor and for flat terminals up to wide of 25mm for conductors: 50-150 SM, 70-185 SE, 35-70 RM/RE					
NAME	SIGNATURE	DATE	DWG NO. C-HEL-4865		A4		
DRAWN S. Pollakowski		01.03.2021	WEIGHT: 0,204kg		SCALE: 1:1		SHEET: 1 OF 1
 Tyco Electronics Raychem GmbH a TE Connectivity Ltd. company Trachenbergring 85 12249 Berlin (Germany)							