

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - TE Connectivity Ltd.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWN	13AUG2019	VM	DH

Ordering Information

VTM3

Series VTM3

Interval
Timing Module

A

Input Voltage

A = 120VAC
E = 24VAC/VDC
Q = 12VAC/VDC

CD

Time Range

CD = 0.5 - 10 sec.
DD = 3 - 60 sec.
GD = 3 - 60 min.

POLARITY SHOWN FOR DC MODELS

Wiring Diagram

2.00 (50.8)

2.00 (50.8)

1.25 (31.8)

.885 (22.5)

.170 DIA (4.32) ACCEPTS #8 SCREW

.250 (6.35) X .032 (.813) QUICK CONNECTS

Outline Dimensions

ALL DIMENSIONS ARE IN INCHES(MM).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VM	13AUG2019	TE Connectivity Ltd.	
		CHK RV	13AUG2019		
		APVD DH	13AUG2019		
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME VTM3 SERIES, INTERVAL,TIMING MODULE	
MATERIAL		FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	SIZE A3 CAGE CODE - DRAWING NO VTM3-SERIES RESTRICTED TO -
CUSTOMER DRAWING				SCALE NTS	SHEET 1 of 1
				REV A	

1470-19 (1/15)