

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - TE Connectivity Ltd.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ORIGINAL ISSUE	02/2020	GR	KP

PHYSICAL PROPERTIES:

1. MINIMUM CREEPAGE DISTANCE : 1120 mm
 2. NOMINAL DRY ARCING DISTANCE : 370 mm

ELECTRICAL PROPERTIES:

1. DRY AC WITHSTAND VOLTAGE : 125 kV
 2. WET AC WITHSTAND VOLTAGE : 110 kV
 3. DRY AC FLASHOVER VOLTAGE : 140 kV
 4. WET AC FLASHOVER VOLTAGE : 120 kV
 5. LIGHTNING IMPULSE WITHSTAND VOLTAGE : 225 kV
 6. LIGHTNING IMPULSE FLASHOVER VOLTAGE : 235 kV

MECHANICAL PROPERTIES:

1. SPECIFIED CANTILEVER LOAD (SCL) : 11 kN
 2. SPECIFIED TENSILE LOAD (STL) : 25 kN

MATERIALS:

1. CORE : ECR FIBERGLASS REINFORCED POLYMER
 2. HOUSING : SILICONE RUBBER
 3. END FITTINGS : HOT DIP GALVANIZED STEEL
 4. STANDARDS : IEC 62217 & IEC 61952



PRODUCT MARKINGS:

1. TE LOGO
 2. SCL 11kN
 3. YEAR & MONTH
 4. BATCH NO #

NOTES:

UNSPECIFIED TOLERANCE

- 1) $\pm(0.04 \times d + 1.5)$ mm WHEN $d < 300$ mm
 2) $\pm(0.025 \times d + 6)$ mm WHEN $d > 300$ mm
 WITH MAX. TOLERANCE OF ± 50 mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GHANSHYAM RANA 10/02/2020	 TE Connectivity				
DIMENSIONS: mm		CHK RAJESH 10/02/2020					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. PUSTHAY 10/02/2020	NAME CLP-11-CM20-225-1120-0-02 EP4112-000				
		PRODUCT SPEC	RESTRICTED TO				
MATERIAL		FINISH	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			WEIGHT	A3	00779	C=INS1653	—
CUSTOMER DRAWING			SCALE	1:1	SHEET	1 OF 1	REV A