

4

3

2

1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
20		20	
© COPYRIGHT 20		ALL RIGHTS RESERVED.	
BY -			


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
-	-		A	ACTIVE RELEASE PER ECO-14-001075	140221	GS AT
			B	REVISED PER ECO-15-018025	151215	SS BP
			C	REVISED PER ECO-18-018279	181109	PF AR
			D	REVISED PER ECN-24-279143	28AUG24	AD MR



PART NUMBER ***	SUPERCEDED NUMBER	SIZE	(COLOR CODE)	MILITARY PART NUMBER	Ø(A) MAX.	Ø(B) MAX.	(C) MAX
MS27488-22-2	-	22	BLACK	MS27488-22-2	.066	.045	.668
MS27488-20-2	-	20	RED	MS27488-20-2	.090	.058	.805
MS27488-16-2	-	16	GREEN	MS27488-16-2	.130	.079	.872
MS27488-12-2	-	12	ORANGE	MS27488-12-2	.170	.125	.841
MS27488-16-3	0613-1-1601	16	BLUE	MS27488-16-3	.130	.079	1.472
MS27488-12-3	0613-1-1201	12	YELLOW	MS27488-12-3	.170	.125	1.441

3. MATERIAL: PLASTIC ROD, MOLDED AND EXTRUDED-TEMPERATURE LIMIT 200°C MINIMUM. POLYPHENYLSULFONE (PPSU) PER ASTM-D6394. (B)
2. (INSULATION RESISTANCE SHALL BE 100 MEGAOHMS MINIMUM WHEN TESTED IN ACCORDANCE WITH ASTM D257.)
1. DIMENSIONS AND TOLERANCES SHOWN FOR REFERENCE ONLY.
- NOTES: UNLESS OTHERWISE SPECIFIED.

DESCRIPTION:
SIZE 22, 20, 16
AND 12 PER MS27488

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G.S.	130918	 TE Connectivity			
DIMENSIONS: INCHES		CHK A. TEUNISSEN	140122				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.005 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.005 4 PLC ±0.0001 ANGLES ±0.5	APVD A. RENGIFO	140221	NAME SEAL, PLUG PER MS27488 ENVELOPE			
		PRODUCT SPEC MS27488					
		APPLICATION SPEC -					
MATERIAL SEE NOTE 3	FINISH -	WEIGHT -		SIZE A3	CAGE CODE 111139	DRAWING NO C-MS27488 - x x - x	RESTRICTED TO -
		Customer Drawing				SCALE 15.000	SHEET 1 OF 1