





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER PCN E-17-012564	28AUG2017	JA	DM
	C	REVISED PER PCN E-19-014633	13FEB2019	AK	NS
	D	REVISED PER PCN-23-192205	06FEB2024	RK	CB

-E- SYMBOL DESIGNATES REDUCED DIAMETER WIRE SEAL



FLANGE SEAL IS INTENDED FOR NON-PRESSURIZED FLUID SPLASH ONLY

2X THREADED INSERT M6 X .500 DEEP RECOMMENDED TORQUE: 62-88 IN-LB [7-10 N-m]

RECOMMENDED MOUNTING DETAIL

4 DATE CODE: MONTH IS REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS. EX: A = JANUARY, YEAR IS REPRESENTED BY LAST NUMERICAL DIGIT. EX: 0 = 2010

3 MATERIAL: HOUSING: PA66 GF15 (GRAY) CAP: PA66 GF15 (BLACK) GROMMET, GASKET: VMQ (BURNT RED) INSERTS: STAINLESS STEEL

2. THIS RECEPTACLE MATES WITH DT06-12SA-XXXX PLUG. (XXXX = ALL MODIFICATIONS) CONSULT FACTORY FOR MODIFICATIONS.

1 FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS, SEE ENVELOPE DRAWING 0425-015-0000.

NOTES: UNLESS OTHERWISE SPECIFIED

TE INTERNAL PN	DEUTSCH PN
DT04-12PA-LE06	DT04-12PA-LE06

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm <sup>2</sup> ] REF ONLY
16	.053 [1.35]	.120 [3.05]	14-20 AWG [2.5-0.5]

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	C. WOODRUFF	14MAR1994
CHK	B. BYFORD	06JUL2012
APVD	S. BEARD	05JUL2012
PRODUCT SPEC	108-151009	
APPLICATION SPEC	114-151009	
WEIGHT	73g	

**TE** TE Connectivity

NAME: 3 WAY RECEPTACLE FLANGE MOUNT THIN WALL WIRE SEAL DT SERIES

SIZE	A3	CAGE CODE	4AFU8	DRAWING NO	DT04-12PA-LE06	RESTRICTED TO
------	----	-----------	-------	------------	----------------	---------------

CUSTOMER DRAWING SCALE 1:1 SHEET 1 OF 1 REV D