


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	29FEB2024	AN	VN



PRODUCT DIMENSIONS

SIZES	AS SUPPLIED		AS RECOVERED					
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		TOTAL WALL THICKNESS AFTER RECOVERY (W)		OUTER JACKET WALL THICKNESS AFTER RECOVERY (WI)	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.
4/1	4.00	0.157	1.00	0.039	0.80±0.15	0.031±0.006	0.50±0.12	0.020±0.005
8/2	8.00	0.315	2.00	0.079	0.90±0.20	0.035±0.008	0.60±0.12	0.024±0.005
12/3	12.00	0.472	3.00	0.118	1.20±0.25	0.047±0.010	0.80±0.15	0.031±0.006
16/4	16.00	0.630	4.00	0.157	1.50±0.25	0.059±0.010	1.00±0.20	0.039±0.008


PRODUCT INFORMATION

- NON-FLAME RETARDANT
- OUTER JACKET: IRRADIATED MODIFIED POLYOLEFIN  
COLOUR: CLEAR  
INNER LINER: HOT MELT ADHESIVE  
COLOUR: LIGHT AMBER  
OTHER COLOURS ARE POSSIBLE BY SPECIAL CONTRACT
- SHRINK RATIO 4:1
- LONGITUDINAL CHANGE 0 TO -15%
- TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm



MATERIAL  
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±0.1  
1 PLC ±0.1  
2 PLC ±0.01  
3 PLC ±0.001  
4 PLC ±0.0001  
ANGLES ±  
FINISH -

DWN	29FEB2024
AYESHABANU N	
CHK	29FEB2024
BASAVARAJA D A	
APVD	29FEB2024
VLADIMIR NEMEC	
PRODUCT SPEC	
RK-6204	
APPLICATION SPEC	
114-120023	
WEIGHT	-
CUSTOMER DRAWING	



NAME  
DWTC-DUAL WALL SLEEVE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-DWTC	-
SCALE		SHEET	REV
NTS		1 OF 1	A