






HARDWARE OPTIONS


CODE: S
STANDARD
SLOTTED
HEAD SCREW



CODE: SSL
SHORT
SLOTTED
HEAD SCREW




CODE: H
HEX SOCKET
HEAD SCREW




CODE: 2H
HEX SOCKET
HEAD SCREW
PLUS SHELL HEX
SOCKET HEAD SCREW

CODE: PF/F
JACK POST
(4-40 UNC)



CODE: 0
NO HARDWARE
SUPPLIED



DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER: DSF**-F-BT-***-**-*		 Polamco			
DIW		19/02/2018								
DESIGN APPROVAL		DATE		UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°	TITLE: 45DEG SPLIT BANDING BACKSHELL					
K. SHEPPARD		20/03/2018								
DOC TYPE	Customer Drawing			MATERIAL SEE PART NUMBER BREAKDOWN	ASSY USED ON: MIL-DTL-24308					
ISSUE AB	REV.	DCR CRN26424								
NCAGE CODE U5792		WEIGHT	-		THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.		POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP		SHT 1	DRAWING NO P15567

DSF25-F-BT-08E-1-C-T-H

CONNECTOR TYPE _____
 SPLIT SHELL, FLANGE MOUNTING _____
 SHELL SIZE _____
 ENTRY POSITION (F - 45°) _____
 TERMINATION STYLE _____
 ENTRY SIZE (TABLE 2A AND 2B) _____
 ELLIPTICAL ENTRY _____
 MATERIAL _____
 ALUMINIUM ALLOY _____
 FINISH (SEE TABLE 3) _____
 T OPTION _____
 OMIT FOR STANDARD FLANGE _____
 HARDWARE OPTION _____
 SEE BELOW FOR CODE 2H DETAILS

TABLE 1

SHELL SIZE	A	B	C	D	L	MAX CIRCULAR ENTRY	MAX ELLIPTICAL ENTRY
09	31,19	25,00	13,00	22,86	35,0	06	07E
15	39,52	33,33	13,00	31,09	40,0	06	08E
25	53,42	47,02	13,00	44,86	40,0	06	09E
37	69,76	63,50	13,00	61,32	46,5	06	11E
50	67,31	61,12	15,80	58,98	46,5	08	12E
104	69,70	63,50	17,90	NA	46,5	09	12E

TABLE 2A

ENTRY SIZE	G
01	3,18
02	4,75
03	6,86
04	7,37
05	7,92
06	10,03
07	10,67
08	12,70
09	14,27

TABLE 2B


ENTRY SIZE	E MIN	F MIN	J
07E	13,00	9,50	18,00
08E	16,50	9,50	21,50
09E	20,50	9,50	25,50
10E	24,70	9,50	29,70
11E	29,40	9,50	34,40
12E	34,60	9,50	39,60
12E (#50 ONLY)	29,40	12,00	34,40

TABLE 3

CODE	FINISH
C	ELECTROLESS NICKEL
B	CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL
CHP	ELECTROLESS NICKEL, HIGH PHOSPHOR
Y	YELLOW CHROMATE OVER CADMIUM
GOLD	GOLD OVER ELECTROLESS NICKEL

SEE SS0076 FOR FULL RANGE OF FINISH OPTIONS

CODE: 2H HARDWARE OPTION



DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:				DSF**-F-BT-***-**-*				 Polamco	
DIW		19/02/2018			TITLE:									
DESIGN APPROVAL		DATE		45DEG SPLIT BANDING BACKSHELL										
K.SHEPPARD		20/03/2018						ASSY USED ON: MIL-DTL-24308						
DOC TYPE	Customer Drawing			UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.							POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP		SHT 2
ISSUE AB	REV.	DCR CRN26424							MATERIAL SEE PART NUMBER BREAKDOWN					
NCAGE CODE U5792		WEIGHT -		FINISH SEE PART NUMBER BREAKDOWN										