


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	06MAR2024	AN	VN
	AI	DRAWING CLARIFICATION	05JUL2024	AN	MB



PRODUCT DIMENSIONS

SIZES	AS SUPPLIED		AS RECOVERED							
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		WALL THICKNESS AFTER RECOVERY (W)					
	mm.	in.	mm.	in.	MINIMUM		MAXIMUM		NOMINAL	
					mm.	in.	mm.	in.	mm.	in.
RPT-120-19/6	19.00	0.748	6.00	0.236	0.92	0.036	1.08	0.043	1.00	0.039
RPT-120-27/12.7	27.00	1.063	12.70	0.500	0.78	0.031	0.94	0.037	0.86	0.034


PRODUCT INFORMATION

- NON-FLAME RETARDANT
- MATERIAL: HEAT SHRINKABLE MODIFIED POLYOLEFIN  
COLOUR: BLACK
- SHRINK RATIO 2:1
- LONGITUDINAL CHANGE -5 TO -15%
- SPECIFIC CUT LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm



MATERIAL  
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
 0 PLC ±:  
 1 PLC ±0.1  
 2 PLC ±0.01  
 3 PLC ±0.001  
 4 PLC ±0.0001  
 ANGLES ±:  
 FINISH -

DWN	06MAR2024
AYESHABANU N	
CHK	06MAR2024
BASAVARAJA D A	
APVD	06MAR2024
VLADIMIR NEMEC	
PRODUCT SPEC	
RK-6765	
APPLICATION SPEC	
-	
WEIGHT	-
CUSTOMER DRAWING	



NAME  
RPT-120

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-RPT-120	-
SCALE		SHEET	REV
NTS		1 OF 1	AI