

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	WALL THICKNESS TOLERANCE ADDED	05JUL2023	KP	YW

EV SINGLE WALL TUBING

PART AS SUPPLIED AND FULLY RECOVERED




TABLE 1: DIMENSIONS mm(inches)

SIZE		INSIDE DIAMETER AS SUPPLIED (MIN) - D		INSIDE DIAMETER AFTER RECOVERY (MAX) - d		WALL THICKNESS AFTER RECOVERY (W)					
mm.	in.	mm.	in.	mm.	in.	MINIMUM		MAXIMUM		NOMINAL	
mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
10/5	3/8	10.00	0.394	4.50	0.177	0.56	0.022	0.72	0.028	0.64	0.025
12.7/6.4	1/2	12.70	0.500	6.40	0.252	0.56	0.022	0.72	0.028	0.64	0.025
20/9.5	3/4	20.00	0.787	9.50	0.374	0.68	0.027	0.84	0.033	0.76	0.030
26/12.7	1	26.00	1.024	12.70	0.500	0.76	0.030	1.01	0.040	0.88	0.035
40/19	1-1/2	40.00	1.575	19.00	0.748	0.86	0.034	1.17	0.046	1.01	0.040
50/25	2	50.00	1.969	25.00	0.984	0.96	0.038	1.32	0.052	1.14	0.045

- HIGH FLAME-RETARDED
- AVAILABLE IN 2:1 EXPANSION RATIO
- COLOR ON RECOVERED TUBE : ORANGE (RAL2003 WITH DELTA E ALLOWABLE UPTO 12)
- REFERENCED SPECIFICATION : 108-120071
- TUBING OF SPECIAL EXPANDED OR RECOVERED DIMENSIONS MAY BE SUPPLIED AS SPECIFIED IN THE CONTRACT OR ORDER
- PRODUCT AVAILABLE IN DIFFERENT CUT LENGTHS

<table border="1"> <thead> <tr> <th>CUT LENGTH</th> <th>CUT LENGTH TOLERANCE</th> </tr> </thead> <tbody> <tr> <td>UP TO 9.9mm</td> <td>±1.5mm</td> </tr> <tr> <td>10 TO 24.9mm</td> <td>±1.5mm</td> </tr> <tr> <td>25 TO 54.9mm</td> <td>±1.5mm</td> </tr> <tr> <td>55 TO 99.9mm</td> <td>±3.0mm</td> </tr> <tr> <td>100 TO 149.9mm</td> <td>±4.0mm</td> </tr> <tr> <td>150 TO 499.9mm</td> <td>±5.0mm</td> </tr> <tr> <td>500mm AND GREATER</td> <td>±25.4mm</td> </tr> </tbody> </table>	CUT LENGTH	CUT LENGTH TOLERANCE	UP TO 9.9mm	±1.5mm	10 TO 24.9mm	±1.5mm	25 TO 54.9mm	±1.5mm	55 TO 99.9mm	±3.0mm	100 TO 149.9mm	±4.0mm	150 TO 499.9mm	±5.0mm	500mm AND GREATER	±25.4mm	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05JUL2023 KAMALASARAVANAN P	TE Connectivity	NAME EVSW (2:1 RATIO) - IRRADIATED MODIFIED POLYOLEFIN SINGLE WALL HEAT SHRINK TUBING	
	CUT LENGTH	CUT LENGTH TOLERANCE																				
	UP TO 9.9mm	±1.5mm																				
	10 TO 24.9mm	±1.5mm																				
	25 TO 54.9mm	±1.5mm																				
	55 TO 99.9mm	±3.0mm																				
	100 TO 149.9mm	±4.0mm																				
150 TO 499.9mm	±5.0mm																					
500mm AND GREATER	±25.4mm																					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED. 0 PLC ±- 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±-	CHK 05JUL2023 SELVAPANDIAN B	SIZE A3	CAGE CODE	DRAWING NO 114-120020	RESTRICTED TO															
MATERIAL			FINISH	APVD 05JUL2023 YIZHEN WANG	PRODUCT SPEC 108-120071	SCALE NTS	SHEET 1 OF 1	REV B														
			APPLICATION SPEC	WEIGHT																		
			CUSTOMER DRAWING																			