


REVISIONS					
REV.	ECN#	ZONE	DESCRIPTION	CHANGED BY/DATE	APPROVED BY/DATE
AA	ECN# 2144	ALL	INITIAL RELEASE	A.M. 13MAR14	S.S. 13MAR14

PARAMETER	PERFORMANCE
MODEL NUMBER	FG4500
FREQUENCY	450 MHZ - 470 MHZ
GAIN	UNITY
POLARIZATION	VERTICAL
TERMINATION	N-FEMALE
IMPEDANCE	50 OHM
RADIATION PATTERN	OMNI-DIRECTIONAL
VSWR	<2:1
POWER RATING	100 WATTS
HEIGHT	~510 MM
WEIGHT	415.5 g
OUTDOOR RATED	YES
OPERATING TEMP	-30°C - +85°C
RECOMMENDED MOUNTING BRACKET	FM2 (NOT INCLUDED)



MATERIAL: N/A		THIRD ANGLE PROJECTION	
FINISH: N/A		DO NOT SCALE DRAWING	
APPROVALS		DATE	
DRAWN BY	A.MASCORRO	13MAR14	
ELEC. ENG.	A.MASCORRO	13MAR14	
MECH. ENG.	S.SAFVI	13MAR14	
MFG./OPS.			
INTERPRET DIMENSIONING AND TOLERANCING IN ACCORDANCE WITH ASME Y14.5M-2009 TOLERANCES UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS ANGLE: ±30' 0 PLACE DECIMAL: ±0.5 1 PLACE DECIMAL: ±0.25 2 PLACE DECIMAL: ±0.13 SURFACE ROUGHNESS 1.6/√			

Laird SCHAUMBURG, IL 60173 USA

TITLE: **FG4500 MOUNTING & OUTLINE**

SIZE	DWG. NO.	REV
A3	FG4500MO	AA
SCALE: 1:3	PREVIOUS#	SHEET 1 OF 1

UNLESS OTHERWISE NOTED, THIS DOCUMENT CONTAINS LAIRD TECHNOLOGIES CONFIDENTIAL INFORMATION. REPRODUCTION, USE, DISCLOSURE OR TRANSMITTAL OF ALL OR ANY PART OF THIS DOCUMENT IS PROHIBITED EXCEPT TO THE EXTENT APPROVED IN WRITING BY AN AUTHORIZED REPRESENTATIVE OF LAIRD TECHNOLOGIES. LAIRD TECHNOLOGIES RESERVES ALL RIGHTS UNDER PATENTS, TRADEMARKS, COPYRIGHTS AND TRADE SECRETS. COPYRIGHT, LAIRD TECHNOLOGIES 2014. ALL RIGHTS RESERVED.