

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

| P | LTR | DESCRIPTION     | DATE      | DWN | APVD |
|---|-----|-----------------|-----------|-----|------|
|   | A   | INITIAL RELEASE | 31MAY2018 | DW  | CW   |
|   | A1  | ECR-21-000654   | 26JAN2021 | BS  | CW   |
|   |     |                 |           |     |      |
|   |     |                 |           |     |      |

NOTES:

1. TECHNICAL CHARACTERISTICS:  
 CONTACT MATERIAL: BRASS  
 SURFACE PLATING:  
 GOLD PLATING:  $\geq 0.125\mu\text{m}$   
 WIRE RANGE: 0.08-0.52 mm<sup>2</sup> (28-20 AWG)  
 OPERATION TEMPERATURE: -40-+125°C

注释:

1. 技术参数:  
 公针材料: 黄铜  
 表面电镀:  
 镀金:  $\geq 0.125\mu\text{m}$   
 接线范围: 0.08-0.52 mm<sup>2</sup> (28-20 AWG)  
 工作温度: -40-+125°C

| GOLD PLATING 镀金 |   | $\phi d$ | $\phi d2$ | WIRE GAUGE 线规   |       | STRIPPING LENGTH 剥线长度 (mm) |
|-----------------|---|----------|-----------|-----------------|-------|----------------------------|
| PART NUMBER 料号  | PART DESCRIPTION 描述                                 |          |           | MM <sup>2</sup> | AWG   |                            |
| T2070021008-000 | DAM-T-08<br>HMN-025公针 0.08-0.21mm <sup>2</sup> , 镀金 | 0.7      | 0.6       | 0.08-0.21       | 28-24 | 4.0                        |
| T2070021013-000 | DAM-T-13<br>HMN-025公针 0.13-0.33mm <sup>2</sup> , 镀金 | 0.9      | 0.8       | 0.13-0.33       | 26-22 |                            |
| T2070021033-000 | DAM-T-33<br>HMN-025公针 0.21-0.52mm <sup>2</sup> , 镀金 | 1.12     | 0.8       | 0.21-0.52       | 24-20 |                            |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 31MAY2018

DAVID WANG

CHK 31MAY2018

GINO YAO

APVD 31MAY2018

CHRIS WANG

PRODUCT SPEC

108-137064

APPLICATION SPEC

114-137064

WEIGHT

-

TE Connectivity

NAME

CAM/DAM  
D-SUB PIN CONTACT

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-T20700210XX000 -

CUSTOMER DRAWING

SCALE 8:1

SHEET 1 OF 1

REV A1

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

|        |    |
|--------|----|
| 0 PLC  | ±- |
| 1 PLC  | ±- |
| 2 PLC  | ±- |
| 3 PLC  | ±- |
| 4 PLC  | ±- |
| ANGLES | ±- |

MATERIAL

-

FINISH

-

1470-19 (3/13)