

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2017

© COPYRIGHT 2017

BY - TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	03JAN2017	VNB	CF

NOTES:

- TAPER OF POST 1 IN 9 TO BS3911 PT.1 1982
- CABLE REF. 416/0.45 OR EQUIVALENT (70mm²)
- CRIMP DIE TO BE 12.5mm ACROSS FLATS AND 10mm WIDE (2 X 5mm WIDE ACCEPTABLE)
- ASSOCIATED PARTS:-
HC5849 -SALEABLE KIT INC. BATT. POST, 5/16" NUT AND BOLT.
HC5841 -BATTERY POST (WHEN SOLD SEPERATELY)
429604 -5/16" NUT (WHEN SOLD SEPERATELY)
429605 -5/16" SQUAR HEAD BOLT (WHEN SOLD SEPERATELY)
- REPLACES OLD DEUTSCH DRAWING D429905 (ENVELOPE DRAWING)

SCALE 1:1

HC5849	1	BRASS	-	INTEGRAL BATTERY POST CLAMP - NEGATIVE (-VE) WITH OPTIONAL NUT AND BOLT	A	1
TE ORDER NO.	QUANTITY	MAT.	COLOUR SURFACE	DESCRIPTION	REV.	ITEM
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN 03JAN2017 VIJETH BHARADWAJ		
DIMENSIONS: mm				CHK 04JAN2017 PRAVEENA V		
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD 18NOV2016 V V BIDI		
				PRODUCT SPEC		
MATERIAL SEE TABLE				FINISH TIN PLATED	NAME INTEGRAL BATTERY POST CLAMP NEGATIVE (-VE) WITH OPTIONAL NUT AND BOLT	
				WEIGHT 66.5g	SIZE A3	CAGE CODE -
				CUSTOMER DRAWING	DRAWING NO. HC5849	RESTRICTED TO -
				SCALE 2:1	SHEET 1 OF 1	REV A

1470-19 (3/13)