


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	22DEC2017	YC	CW
	AI	ECR-18-018540	07DEC2018	AL	CW

ASSEMBLY STATE OF THE PRODUCT, FOR REFERENCE

产品装配状态, 供参考



NOTES:


- TECHNICAL CHARACTERISTICS:
 INSULATION MATERIAL: PC
 RATED VOLTAGE: 50V
 RATED CURRENT: 10A
 RATED IMPULSE VOLTAGE: 0.8KV
 POLLUTION DEGREE: 3
 FLAMMABILITY: UL94V-0
 WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
 CABLE DIAMETER: 3 - 9.5 mm
 CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.

注释:



- 技术参数:
 绝缘材料: PC
 额定电压: 50V
 额定电流: 10A
 额定脉冲电压: 0.8KV
 污染等级: 3
 阻燃等级: UL94V-0
 接线范围: 0.14-2.5 mm² (26-14 AWG)
 电缆外径: 3-9.5 mm
 接线类型: 冷压接
- 端子需要单独订购.

FOR ∅6-9.5mm CABLE
用于直径 ∅6-9.5mm 电缆线

FOR ∅3-6mm CABLE
用于直径 ∅3-6mm 电缆线



T2580031154-007	PIN-Q2-M	QUINTAX MALE CONTACT 4-POS QUINTAX 4-POS 公针
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22DEC2017 YORK CHEN	 TE Connectivity	
		CHK 22DEC2017 GINO YAO		
		APVD 22DEC2017 CHRIS WANG		
		PRODUCT SPEC 108-137067		
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-	APPLICATION SPEC 114-137067	NAME QUINTAX CONTACT 4-POS PIN-Q2-M
MATERIAL -		FINISH -	WEIGHT -	SIZE A3
CUSTOMER DRAWING			SCALE 2:1	CAGE CODE 00779
			DRAWING NO T2580031154007	RESTRICTED TO -
			SHEET 1	OF 1
			REV AI	