


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	22FEB2016	DW	CW
	A1	ECR-19-004297	22MAR2019	SR	CW
	A2	ECR-24-224231	11NOV2024	SC	RB



NOTES:

I. TECHNICAL CHARACTERISTICS:

SHELL MATERIAL / 主体材料 : BRASS, NICKEL PLATED / 铜镍镀铬

O RING / O 型圈: NBR

OPERATION TEMPERATURE / 工作温度: -40°C +100°C

M40x1.5	34	43	38.2	21.5	15	M40x1.5	STUD-M40 金属轴套—圆形M40-M40	T3333404011-000	
M32x1.5	27	34.5	30.2	21.5	15	M32x1.5	STUD-M32 金属轴套—圆形M32-M32	T3333323211-000	
M25x1.5	20.5	27.2	23.2	20	13.5	M25x1.5	STUD-M25 金属轴套—圆形M25-M25	T3333252511-000	
M20x1.5	15.5	22	18.2	18	11.5	M20x1.5	STUD-M20 金属轴套—圆形M20-M20	T3333202011-000	OBSOLETE
PG29	32	39	35.5	21.5	15	PG29	STUD-PG29 金属轴套—圆形PG29-PG29	T3333292912-000	
PG21	24	30	26.5	20	13.5	PG21	STUD-PG21 金属轴套—圆形PG21-PG21	T3333212112-000	
PG16	18	24.5	21	18	11.5	PG16	STUD-PG16 金属轴套—圆形PG16-PG16	T3333161612-000	OBSOLETE
PG13.5	16	22.4	18.9	18	11.5	PG13.5	STUD-PG13.5 金属轴套—圆形PG13.5-PG13.5	T3333131312-000	
M1-6H M1-6H 内螺纹	D	D1	D2	H	L	M2-6g M2-6g 外螺纹	PART DESCRIPTION 描述	PART NUMBER 料号	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 19FEB2016 DAVID WANG CHK 19FEB2016 CHRIS WANG APVD 19FEB2016 XIANG XU		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Circle Metal Thread Adapter	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	
MATERIAL - -		CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779
				DRAWING NO C-T3333XXXX1X000	
				SCALE 2:1	SHEET 1 of 1
				REV A2	