


P	LTR	DESCRIPTION	DATE	DWN	APVD
	AI	REVISED PER ECN-24-267994	28MAY2024	SJ	JH



NOTES: UNLESS OTHERWISE SPECIFIED.


1. FABRICATE TO MEET IPC - 6013, CLASS 2.
INSPECT TO MEET IPC - A - 600, CLASS 2.
2. MATERIAL :
A. PI FILM + VHB DOUBLE SIDED ADHESIVE.
B. CABLE : COAX CABLE DIA 1.13.
CABLE CONN: I-PEX or TE APPROVED EQUIVALENT.
3. FINISH:
A: SOLDERMASK BOTH SIDES: ORANGE.
4. PACKAGING: SINGULATED PARTS TO BE SECURELY
BAG WRAPPED, BAGGED OR VACUUM PACKED IN BULK.
5. GENERAL TOLERANCE IS ± 0.2
6. CONSULT TE CONNECTIVITY DATA SHEET DS-2108965.
7. SILKSCREEN; WHITE EPOXY INK
A. TE LOGO, TE P/N
B. WORD REV., FOLLOWED BY THE LATEST REVISION LETTER, AS SHOWN.
C. 4 DIGIT DATE CODE: FIRST 2 DIGITS FOR THE
WEEK CODE AND THE 2ND TWO DIGITS FOR THE YEAR CODE.
OTHERS: SPECIFIC TE SOURCE CODE NUMBER DIGITS AS REQUIRED

UMCC GEN4 MHF4L	(154.80)	1.13	150.00	L000528-06
	(104.80)	1.13	100.00	L000528-05
	(54.80)	1.13	50.00	L000528-04
UMCC GEN1 MHF	(154.80)	1.13	150.00	L000528-03
	(104.80)	1.13	100.00	L000528-02
	(54.80)	1.13	50.00	L000528-01
CONNECTOR TYPE "C"	(C)	"B" CABLE OD	"A" CABLE LENGTH	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.J. NOH		27JUN2023		 TE Connectivity	
		CHK					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JH.KIM		NAME FPC ANT, MHF/MHF4L, LPWAN 868MHZ	
		0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2	
		MATERIAL SEE NOTE -		CAGE CODE 00779		DRAWING NO C-L000626	
CUSTOMER DRAWING				SCALE 2:1		SHEET 1 of 2	
						REV A1	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


PACKAGING



25 PCS/Bundle




50pcs/Bag
drying agent: 1pcs/Bag





Number of label

- Importance of check:
1. Check whether the product is out of shape before packing.
 2. When packing, handle the product lightly to avoid product distortion.
 3. After packed, check whether there is any miss and whether the product is placed in the correct direction.
 4. If there are unfilled boxes, fill them with buffer materials.
 5. After the Carton is sealed, check whether the label is properly affixed, clean, legible, and whether the label content is correct.
 6. Carton size (604010011) : L340*W240*H230mm


Package materials			Packing Spec		
Items	P/N	QTY	PCS/Bag	Bag/Box	PCS/Box
Carton	604010011	1	50	40	2000
Small PE bag	840000511	40			
Waterproof bag	840000502	1			
Foam		2			
Drying agent	708040129	40			




40 Bag/Box
(2000PCS/Box)



Carton Label



Carton Label

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.J. NOH	27 JUN 2023	 TE Connectivity		
DIMENSIONS: mm		CHK				
		APVD JH. KIM	27 JUN 2023	NAME FPC ANT, MHF/MHF4L, LPWAN 868MHz		
		PRODUCT SPEC		-		
MATERIAL SEE NOTE		APPLICATION SPEC		SIZE A2		
		WEIGHT		CAGE CODE 00779		
		CUSTOMER DRAWING		DRAWING NO C-L000626		
				RESTRICTED TO -		
				SCALE 2:1		
				SHEET 2 OF 2		
				REV A1		