


P	LTR	DESCRIPTION	DATE	DWN	APVD



Parameter	Performance		
Part Number	OC24716-FNM		
TCPN	L000659-02		
Frequency Bands, MHz	2400-2500	4900-6000	6000-7125
Peak Gain, dBi	3	6	6
Total Efficiency (Avg,%)	>70%		
Pattern E plane, H-plane	E:50 H:360	E:20 H:360	E:20 H:360
VSWR (Max)	<2:1		
Nominal Impedance	50 Ω		
Polarization	Linear, Vertical		
Cross Polarization Ratio	9:1		
Input Power (Max)	33dBm		
Temperature Range	-40°C ~ +70°C		
Weight	137g		
RF Connector	TYPE N, ROTATABLE MALE		
Housing Material	PC, UV STABILIZE		
Housing Color	WHITE		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CY HANG	07SEP2023														
DIMENSIONS: mm		CHK KM LIM	07SEP2023														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD WT NG	07SEP2023	NAME OMNI, TBAND, NM, 2.4-5-7.125GHZ ANT-2x2, NM													
<table border="0"> <tr> <td>0 PLC</td> <td>±-</td> </tr> <tr> <td>1 PLC</td> <td>±0.5</td> </tr> <tr> <td>2 PLC</td> <td>±0.13</td> </tr> <tr> <td>3 PLC</td> <td>±0.013</td> </tr> <tr> <td>4 PLC</td> <td>±0.0001</td> </tr> <tr> <td>ANGLES</td> <td>±0.5</td> </tr> </table>		0 PLC	±-	1 PLC	±0.5	2 PLC	±0.13	3 PLC	±0.013	4 PLC	±0.0001	ANGLES	±0.5	PRODUCT SPEC 108-161123	DRAWING NO L000659-02		RESTRICTED TO -
0 PLC	±-																
1 PLC	±0.5																
2 PLC	±0.13																
3 PLC	±0.013																
4 PLC	±0.0001																
ANGLES	±0.5																
MATERIAL TBD material_2	FINISH -	APPLICATION SPEC -	WEIGHT -	SIZE A3	CAGE CODE 00779												
CUSTOMER DRAWING			SCALE 1:2	SHEET 1 OF 1	REV A												