


6 5 4 3 2 1

REVISIONS					
REV.	ECR#	ZONE	DESCRIPTION	CHANGED BY/DATE	APPROVED BY/DATE
A	SCH-90003		Initial Release	PFR 9/7/2012	

APPROVED
By barb.potulski at 1:14 pm, 1/4/13

Parameter	Performance
Model Number Laird Technologies	MAB8UMI16.5
Mount Type	NMO Mount
Frequency (MHz)	< 3 GHz
Weight (Mount) (lbs)	6 oz
Storage Temp. Range (°C)	-40°C to +85°C
Operating Temp. Range (°C)	-35°C to +80°C
Outdoor Rated	Yes
Cable Length	5.03 m
Cable Type	RG58U
Connector Type	Mini - UHF



UNLESS OTHERWISE NOTED, THIS DOCUMENT CONTAINS LAIRD TECHNOLOGIES CONFIDENTIAL INFORMATION. REPRODUCTION, USE, DISCLOSURE OR TRANSMITTAL OF ALL OR ANY PART OF THIS DOCUMENT IS PROHIBITED EXCEPT TO THE EXTENT APPROVED IN WRITING BY AN AUTHORIZED REPRESENTATIVE OF LAIRD TECHNOLOGIES. LAIRD TECHNOLOGIES RESERVES ALL RIGHTS UNDER PATENTS, TRADEMARKS, COPYRIGHTS AND TRADE SECRETS. COPYRIGHT, LAIRD TECHNOLOGIES 2010, ALL RIGHTS RESERVED.

MATERIAL: N/A		THIRD ANGLE PROJECTION		Schaumburg, IL 60173 USA	
FINISH: N/A		 DO NOT SCALE DRAWING			
APPROVALS		DATE		TITLE: MOUNT, BMM, 3/8, 58U, MUHFF	
DRAWN BY	<i>[Signature]</i>			MOUNT & OUTLINE DRAWING	
PROJ. ENG.	<i>[Signature]</i>			INTERPRET DIMENSIONING AND TOLERANCING IN ACCORDANCE WITH ASME Y14.5M-2009 TOLERANCES UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	
APPL. MECH.				SIZE	DWG. NO.
MFG.				A3	MAB8UMI16.5 - MO
				SCALE: 1:1	PREVIOUS#
				REV A	
				SHEET 1 OF 1	

6 5 4 3 2 1