



POTTER & BRUMFIELD 30A PCB RELAY T9G SERIES

TE Connectivity (TE)'s Potter & Brumfield T9G relay series is a 30A Power PCB relay for HVAC, appliance and industrial control applications. The T9G relay is the smallest relay in its class with a 30% smaller package size and 13% less PCB floor space all while keeping the standard footprint, allowing manufacturers to add more components on PCBs without having to compromise on relay performance. By having both UL and VDE certifications, TE's P&B relay T9G series is a versatile relay that can be used globally and through its PCB and quick connect terminations, it is user-friendly and easy to install.

BENEFITS

- Save PCB space with the smallest relay in its class while maintaining standard footprint
- Achieve a global relay solution with both UL and VDE certifications
- Help provide operator safety through increased insulation (UL 61810-1)
- Increase relay performance through 4kV dielectric rating / 8kV surge voltage between coil and contacts

APPLICATIONS

- HVAC
- Appliances
- Industrial Controls
- Energy Management

Visit te.com/T9G for a product sample

Potter & Brumfield 30A PCB Relay T9G Series

ELECTRICAL

- **Rated current:** 30 A
- **Rated voltage:** 480 VAC Max.

MECHANICAL

- **Contact arrangement:** 1 form A (NO), 1 form B (NC), 1 form C (CO)
- **PCB mounting or PCB mounting with quick connects**
- **Wash-tight (with knock off nib) or Flux-proof plastic case**


MATERIALS

- **Contact Material:** AgSnO

SPECIFICATIONS

- UL 508
- UL E214025
- IEC 61810-1
- VDE 40045012
- [Data sheet](#)

PRODUCT CODE STRUCTURE



Potter & Brumfield 30A PCB Relay T9G Series

PRODUCT SELECTION INFORMATION

Flux-proof plastic case (requires mounting code 1 or 2)



PCB TERMINALS

Product Code	Contacts	Coil	Part Number
T9GV5L14-5	1 CO	5VDC	1558660-1
T9GV5L14-9		9VDC	1558660-2
T9GV5L14-12		12VDC	1558660-3
T9GV5L14-15		15VDC	1558660-4
T9GV5L14-18		18VDC	1558660-5
T9GV5L14-22		22VDC	1558660-6
T9GV5L14-24		24VDC	1558660-7
T9GV5L14-48		48VDC	1558660-8
T9GV5L14-110		110VDC	1558660-9
T9GV1L14-5		1 NO	5VDC
T9GV1L14-9	9VDC		1558661-2
T9GV1L14-12	12VDC		1558661-3
T9GV1L14-15	15VDC		1558661-4
T9GV1L14-18	18VDC		1558661-5
T9GV1L14-22	22VDC		1558661-6
T9GV1L14-24	24VDC		1558661-7
T9GV1L14-48	48VDC		1558661-8
T9GV1L14-110	110VDC		1558661-9
T9GV2L14-5	1 NC		5VDC
T9GV2L14-9		9VDC	1558662-2
T9GV2L14-12		12VDC	1558662-3
T9GV2L14-15		15VDC	1558662-4
T9GV2L14-18		18VDC	1558662-5
T9GV2L14-22		22VDC	1558662-6
T9GV2L14-24		24VDC	1558662-7
T9GV2L14-48		48VDC	1558662-8
T9GV2L14-110		110VDC	1558662-9

PCB + QUICK CONNECT

Product Code	Contacts	Coil	Part Number
T9GV5L24-5	1 CO	5VDC	1558670-1
T9GV5L24-9		9VDC	1558670-2
T9GV5L24-12		12VDC	1558670-3
T9GV5L24-15		15VDC	1558670-4
T9GV5L24-18		18VDC	1558670-5
T9GV5L24-22		22VDC	1558670-6
T9GV2L24-24	1 NC	24VDC	1558672-7
T9GV2L24-48		48VDC	1558672-8
T9GV2L24-110		110VDC	1558672-9

Potter & Brumfield 30A PCB Relay T9G Series

Wash-tight plastic case with knock off nib (requires mounting code 1 or 2)

PCB TERMINALS




PCB + QUICK CONNECT



Product	Contacts	Coil	Part Number
T9GS5L14-5	1 CO	5VDC	1558665-1
T9GS5L14-9		9VDC	1558665-2
T9GS5L14-12		12VDC	1558665-3
T9GS5L14-15		15VDC	1558665-4
T9GS5L14-18		18VDC	1558665-5
T9GS5L14-22		22VDC	1558665-6
T9GS5L14-24		24VDC	1558665-7
T9GS5L14-48		48VDC	1558665-8
T9GS5L14-110		110VDC	1558665-9
T9GS1L14-5	1 NO	5VDC	1558666-1
T9GS1L14-9		9VDC	1558666-2
T9GS1L14-12		12VDC	1558666-3
T9GS1L14-15		15VDC	1558666-4
T9GS1L14-18		18VDC	1558666-5
T9GS1L14-22		22VDC	1558666-6
T9GS1L14-24		24VDC	1558666-7
T9GS1L14-48		48VDC	1558666-8
T9GS1L14-110		110VDC	1558666-9
T9GS2L14-5	1 NC	5VDC	1558667-1
T9GS2L14-9		9VDC	1558667-2
T9GS2L14-12		12VDC	1558667-3
T9GS2L14-15		15VDC	1558667-4
T9GS2L14-18		18VDC	1558667-5
T9GS2L14-22		22VDC	1558667-6
T9GS2L14-24		24VDC	1558667-7
T9GS2L14-48		48VDC	1558667-8
T9GS2L14-110		110VDC	1558667-9


Product	Contacts	Coil	Part Number
T9GS5L24-5	1 CO	5VDC	1558675-1
T9GS5L24-9		9VDC	1558675-2
T9GS5L24-12		12VDC	1558675-3
T9GS5L24-15		15VDC	1558675-4
T9GS5L24-18		18VDC	1558675-5
T9GS5L24-22		22VDC	1558675-6
T9GS5L24-24		24VDC	1558675-7
T9GS5L24-48		48VDC	1558675-8
T9GS5L24-110		110VDC	1558675-9
T9GS1L24-5	1 NO	5VDC	1558676-1
T9GS1L24-9		9VDC	1558676-2
T9GS1L24-12		12VDC	1558676-3
T9GS1L24-15		15VDC	1558676-4
T9GS1L24-18		18VDC	1558676-5
T9GS1L24-22		22VDC	1558676-6
T9GS1L24-24		24VDC	1558676-7
T9GS1L24-48		48VDC	1558676-8
T9GS1L24-110		110VDC	1558676-9
T9GS2L24-5	1 NC	5VDC	1558677-1
T9GS2L24-9		9VDC	1558677-2
T9GS2L24-12		12VDC	1558677-3
T9GS2L24-15		15VDC	1558677-4
T9GS2L24-18		18VDC	1558677-5
T9GS2L24-22		22VDC	1558677-6
T9GS2L24-24		24VDC	1558677-7
T9GS2L24-48		48VDC	1558677-8
T9GS2L24-110		110VDC	1558677-9

PRODUCT SELECTION INFORMATION



1969656-1

.250 FASTON Flag Housing
Left Hand, Single Position



1969657-1

.250 FASTON Flag Housing
Right Hand, Single Position


- Fully enclosed with TPA cover
- Back is flat to aid assembly and improve ergonomics
- VO 150°C Nylon material
- Used with 2238171-3 (RH) or 2238209-3 (LH) STANDARD 2D FASTONS with low insertion force
- Terminals easily inserted into housings without tooling

2 POSITION HOUSINGS



1969900-1

250 FASTON Flag Housing
Left Hand Flag, 2 position



1-521785-1

250 FASTON Receptacle Housing
2 Position Straight

- Fully enclosed flag housings with TPA cover
- Fully enclosed 2/ TPA cover
- Back is flat to aid assembly and improve ergonomics
- VO 150°C Nylon material
- Used with 2238171-3 (RH) or 2238209-3 (LH) STANDARD 2D FASTONS with low insertion force
Terminals easily inserted into housings without tooling
- Poke Yokes application
- VO GWT 130C Nylon material
- Used with 63306-2 or 63435-1 FASTONS

te.com

Potter & Brumfield TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2019 TE Connectivity. All Rights Reserved.

1-1773924-8 12/19 AK