




# ENTRELEC

©  
\$  
®  
-M


- 0

- 3

- 0




0075



1

ENTRELEC®



2

§



3


ESSAILEC®\$

4@



6

R




6

ð




7

XS-001



8


ð



9

⚡

3303



4


P®



4

PVC®


⊕



10

IP®

⊕




5

PVC®



12

⊕



11

M8/M12/RJ45  
h

## B

SNACOMPACT	-----	P4
SNKBI-A	-----	P9
SNK	-----	P13

## F

DBL	-----	P17
DBLK PI-A	-----	P21
CBST	-----	P23

## H30

WFPH@	-----	P26
PVCP	-----	P30
IP	-----	P34
SNG	-----	P40

## 4

HTP600W	-----	P42
T2212W	-----	P44



# SNACOMPACT

3 k 0

## SNACOMPACT

SNACompact 30% 5y b03 nHHC™  
T#
















































### BT6\*








- ENTRELEC 30% 5y b03 nHHC™
- SNA30 2.54-mm 2 30 414% 40e y53\$
- D603 30% 5y b03 nHHC™







### 08

- ENTRELEC 30% 5y b03 nHHC™
- TE Connectivity H6™
- TE Connectivity 30% 5y b03 nHHC™
- TE Connectivity E.COM Easy Rail Designer 3D CAD


















		mm / AWG	E mm / in	b IEC / UL	b	MÉ	S	S	O		C	
									Ø	fi	Ø	fi
		2.5 / - 2.5/14 4/12	5/0.200	24 A 20 A		& Ø	C2.5/5 C2.5/5.N	1SNL605010R0000 1SNL605020R0000	 EP5-6 1SNL900100R0000	2 3 5 10	1SNL905602R0000 1SNL905603R0000 1SNL905605R0000 1SNL905610R0000	
												
		4 / - 4/12 6/10	6/0.240	32 A 30 A		& Ø	C4/6 C4/6.N	1SNL606010R0000 1SNL606020R0000				
												
		4 / - 4/10	6/0.240	32 A 20 A		& Ø	M4/6.3A M4/6.3A.N	1SNA115468R2000 1SNA125468R2200				
												
	4 / - 4/10	6/0.240	32 A 20 A		& Ø	M4/6.4A M4/6.4A.N	1SNA115479R2300 1SNA125479R2500					
									480 A/1s		o/ç	M4/6.4A.P
	6 - 6/10 10/8	8/0.310	41 A 45 A		& Ø	C6/8 C6/8.N	1SNL608010R0000 1SNL608020R0000					
									10 - 10/8 16/6	10/0.390	57 A 59 A	
	16 - 16/6 16/4	12/0.470	57 A 59 A		& Ø	C16/12 C16/12.N	1SNL612010R0000 1SNL612020R0000					
									1200 A/1s		o/ç	C10/10.P
	35 - - 50/0	16/0.630	125 A 150 A		& Ø	M35/16 M35/16.N	1SNA115124R0700 1SNA125124R0100					
									70 - - 95/00	22/0.866	192 A 159 A	
	95 - - 120/0000	26/1.024	232 A 1230 A		& Ø	D95/26 D95/26.N	1SNA400370R2400 1SNA400371R1100					
									8400 A/1s		o/ç	D70/22.P
	232 A 1230 A		o/ç	D95/26.P	1SNA400620R1700							
							2.5 / - 4/12	5/0.200	24 A 20 A		& Ø	MA2.5/5.D2 MA2.5/5. D2.N
	2.5 / - 4/12	5/0.200	24 A 20 A		&							
							4 / - 4/12	6/0.236	32 A 20 A		& Ø	M4/6.D2 M4/6.D2.N
	4 / - 4/12	6/0.236	32 A 20 A		& Ø							
							4 / - 4/12	6/0.236	20 A 25 A		&	M4/6.DD M4/6.DD1
	6 / - 10/8	8/0.315	41 A 50 A		&							
							6 / - 10/8	8/0.315	41 A 50 A		&	M6/8.D1

	线径 mm <sup>2</sup> / AWG	间距 mm / in	电流 IEC / UL	功能	颜色	型号	产品料号	端板		短路条	
								产品料号	极数	产品料号	
<b>三层</b>  	4 / - - 4/12	6/0.236	32 A 20 A		&	D4/6.T3	1SNA299683R0100	OØ	2 3 5 10	1SNA173217R2600 1SNA173218R0700 1SNA173221R2200 1SNA173226R2700	
	4 / - - 4/12	6/0.236	32 A 20 A		&	D4/6.T3.P	1SNA299684R0200				
	4 / - - 4/12	6/0.236	32 A 20 A		ä	D4/6.T1	1SNA199219R0300				
	4 / - - 4/12	6/0.236	480 A/1s		ç o	D4/6.P.T1	1SNA199220R0000				
<b>分断</b>   	2.5 / - - 4/12	5/0.200	10A		&	MA2.5/5.SNB	1SNA115699R2000	FEM6 1SNA118368R1600	2 10	1SNA113542R1000 1SNA113544R1200	
	4 / - - 4/12 6/10	6/0.236	24A		&	C4/6.S	1SNL606310R0000	EP5-6 1SNL900100R0000	2 3 10	1SNA113546R1400 1SNA116536R0500 1SNA113548R2600	
	6 / - - 10/8	6/0.236	20A		&	M4/6.SNB	1SNA115986R0000	FEM62 1SNA114994R0700	10	1SNA163311R2200	
	4 / - - 4/10	8/0.315	20A		&	M6/8.SNB	1SNA115688R2500	FEM8 1SNA113373R2600	2 3 10	1SNA116538R1700 1SNA116539R1000 1SNA163313R2400	
	4 / - - 4/10	6/0.236	10A		&	M4/6. D2.SNBT	1SNA115561R1500	FEMS6D 1SNA116591R0500	2 3 5 10	1SNA179668R2000 1SNA179669R2100 1SNA179671R1300 1SNA179672R1400	
<b>保险丝</b>   	4 / - - 4/12 4/10	6/0.236	6.3A		è	C4/6.SF	1SNL606410R0000	EP5-6 1SNL900100R0000	2 3 10	1SNA113546R1400 1SNA116536R0500 1SNA113548R2600	
	4 / - - 4/12 4/10	6/0.236	6.3A		è	C4/6.SFD24 C4/6.SFD250	1SNL606411R0000 1SNL606412R0000				
	4 / - - 6/12	8/0.315	6.3A		&	C4/8.SF	1SNL608410R0000	FEM8S 1SNA116951R1500	10	1SNA163311R2200	
	4 / - - 6/12	8/0.315	6.3A		&	M4/8.SFD3	1SNA115935R0400				
	4 / - - 6/12	8/0.315	6.3A		&	M4/8.D2.SF	1SNA115604R2100	FEM8D2S 1SNA116913R0700	2 3 5 10	1SNA176669R1600 1SNA176670R1300 1SNA176672R0100 1SNA176673R0200	
	4 / - - 6/12	8/0.315	6.3A		&	M4/8. D2.SFD3	1SNA115936R0500				
<b>测试与测量</b>  	6 / - - 6/8 10/8	8/0.310	40 A 37 A		&	C6/8.ST1 C6/8.ST1. IP20	1SNL608310R0000 1SNL608311R0000	EP8-ST 1SNL900102R0000	2 10 4/6 4/7 4/6 4/8 4/10 3/4	1SNA116538R1700 1SNA163313R2400 1SNA400849R0000 1SNA400842R0000 1SNA400711R0600 1SNA400712R0700 1SNA400713R0000 1SNA400724R0300	
	6 / - - 10/8		40 A 30 A			M6/8.ST1	1SNA115237R10000				
<b>热电偶</b> 	0_ 0,9° 1,5 mm	6/0.240	-		&	MTC6	1SNA115206R2200	FEM6 1SNA118368R1600	-	-	

	3E mm / AWG	K mm / in	b IEC / UL	b	MÉ	S	b	O		C	
								b	fi	b	
ML+/ y		2.5/- - 2.5/12	6/0.240	22 A 26 A		&	D2.5/6.D	1SNA115542R1200	FED3E 1SNA116771R2000	2 3 5 10	1SNA178024R2500
				D2.5/6.DL			1SNA115537R0500	1SNA178025R2600			
E		1.5/- - 1.5	4/0.157	17.5A		&	DR1.5/4	1SNA110106R2500	FED2-4 1SNA215580R2100	2 3 5 10	1SNA205735R0600
		1.5/- - 2.5/12	5/0.197	20 A 20 A			DR1.5/5	1SNA115510R1600			1SNA205736R0700
		4 - - 4/12	6/0.240	30 A 20 A			DR4/6 DR4/6.N	1SNA110251R0500 1SNA120251R0700			1SNA205737R0000
		4 - - 4/12	6/0.240	480 A/1s		o/ ç	DR4/6.P	1SNA160496R2600	FEDR5 1SNA117318R2300	2 3 4 10	1SNA176704R0200
				1SNA117318R2300			1SNA176705R0300				
								FEDR61 1SNA117600R0300			1SNA176706R0400
											1SNA176708R1600



		mm / in	E	S	b
B		5.2 / 0.205		BAZ1	1SNK900002R0000
		10 / 0.394		BAM4	1SNK900001R0000
		10 / 0.394		BAZH1	1SNK900102R0000
E	yHTP600j	5 x 10/0.197 x 0.394		RC510TT	1SNA231600R1500
		6 x 10/0.236 x 0.394		RC610TT	1SNA233600R1700
		8x 10/0.315 x 0.394		RC810TT	1SNA234600R1000
		105 x 5.2/4.134 x 0.205	yHTP600A	CPMF05105	1SNA235618R0000
	yAMS600/AMS300KA	5 x 5/0.197 x 0.197		RC55	1SNA230000R1200
		5 x 6/0.197 x 0.236		RC65	1SNA232000R0000
		5 x 8/0.197 x 0.315		RCAL85	1SNA237000R0500
		10x4/0.394 x 0.157		RC410	1SNA229000R1500
		10 x 5/0.394 x 0.197		RC510	1SNA231000R0700
		10 x 6/0.394 x 0.236		RC610	1SNA233000R0100
		10 x 8/0.394 x 0.315		RC810	1SNA234000R0200
		10 x 10/0.394 x 0.394		RC1010	SNA238000R1600




# SNK Ø8

PI-Ø



7/4



Ø



PI-Ø



#



Ø



# SNK20 ENTRELEC

PI-A0 2.516 mm

2 - 12 AWG

2



PI-S  
SERIES  
SNK


1500 VDC

3



PI-S  
SERIES  
SNK

1500 VDC



PI-S  
SERIES  
SNK

1500 VDC

4



0  
0  
i  
P  
H

2x2




0  
0  
i  
H

3x2



0  
0  
i




E00

0  
0

0  
0



SNK20  
PI-A0



SNK20

PI-A0

35.2216 mm

2 - 26 AWG

ENTRELEC30

PI-A0

1  
E/

yú



PI-A0  
90%  
ECE6  
0  
ECM  
20%  
8K



→  
A  
HC  
K  
3  
0  
%



ECH  
50%  
3  
K  
PI-A0  
H  
OCA.  
86 FHB



SNK20  
PI-A0

	mm / mm AWG / in	IEC / UL	b*	MÉY	\$	廠	廠	廠	廠	廠	廠
2CE0	2.5 / -	5.2 /	24A		& ð	ZK2.5	1SNK705010R0000	1SET111010R0000	EK2.5 1SNK705910R0000	2	1SNK905302R0000
	2.5 / 14	0.205	20A		o-ç	ZK2.5-BL	1SNK705020R0000	1SET111029R0000		3	1SNK905303R0000
	4 / 12	0.205	300 A/1s 396 A/1s		o-ç	ZK2.5-PE	1SNK705150R0000			5	1SNK905305R0000
	4 / -	6 /	32A		ð	ZK4	1SNK706010R0000	1SET111014R0000	EK2.5 1SNK705910R0000	2	1SNK906302R0000
	4 / 12	0.236	30A		ð	ZK4-BL	1SNK706020R0000	1SET111033R0000		3	1SNK906303R0000
	6 / 10	0.236	480 A/1s 636 A/1s		o-ç	ZK4-PE	1SNK706150R0000			5	1SNK906305R0000
	6 / -	8 /	41A		ð	ZK6	1SNK708010R0000	1SET111016R0000	EK2.5 1SNK705910R0000	2	1SNK908302R0000
	6 / 10	0.315	50A		ð	ZK6-BL	1SNK708020R0000	1SET111035R0000		3	1SNK908303R0000
	10 / 8	0.315	720 A/1s 1008 A/1s		o-ç	ZK6-PE	1SNK708150R0000			5	1SNK908305R0000
	10 / -	10 /	57A		ð	ZK10	1SNK710010R0000	1SET111018R0000	EK10 1SNK710910R0000	2	1SNK910302R0000
	10 / 8	0.394	65A		ð	ZK10-BL	1SNK710020R0000	1SET111037R0000		3	1SNK910303R0000
	16 / 6	0.394	1200 A/1s 1596 A/1s		o-ç	ZK10-PE	1SNK710150R0000			5	1SNK910305R0000
16 / -	12 /	76A		ð	ZK16	1SNK712010R0000	1SET111020R0000	EK10 1SNK710910R0000	2	1SNK912302R0000	
16 / 6	0.472	85A		ð	ZK16-BL	1SNK712020R0000	1SET111039R0000		3	1SNK912303R0000	
25 / 4	0.472	1960 A/1s 2544 A/1s		o-ç	ZK16-PE	1SNK712150R0000			5	1SNK912305R0000	
3CE0	2.5 / -	5.2 /	24A		& ð	ZK2.5-3P	1SNK705010R0000	1SET111010R0000	EK2.5-3P 1SNK705911R0000	2	1SNK905302R0000
	2.5 / 14	0.205	20A		o-ç	ZK2.5-3P-BL	1SNK705021R0000	1SET111029R0000		3	1SNK905303R0000
	4 / 12	0.205	300 A/1s 396 A/1s		o-ç	ZK2.5-PE-3P	1SNK705151R0000			5	1SNK905305R0000
	4 / -	6 /	32A		ð	ZK4-3P	1SNK706011R0000	1SET111014R0000	EK2.5-3P 1SNK705911R0000	2	1SNK906302R0000
	4 / 12	0.236	30A		ð	ZK4-3P-BL	1SNK706021R0000	1SET111033R0000		3	1SNK906303R0000
	6 / 10	0.236	480 A/1s 636 A/1s		o-ç	ZK4-PE-3P	1SNK706151R0000			5	1SNK906305R0000
	6 / -	8 /	41A		ð	ZK6-3P	1SNK708011R0000	1SET111016R0000	EK6-3P 1SNK708911R0000	2	1SNK908302R0000
	6 / 10	0.315	50A		ð	ZK6-3P-BL	1SNK708021R0000	1SET111035R0000		3	1SNK908303R0000
10 / 8	0.315	720 A/1s 1008 A/1s		o-ç	ZK6-PE-3P	1SNK708151R0000		5		1SNK908305R0000	
4CE0	2.5 / -	5.2 /	24A		& ð	ZK2.5-4P	1SNK705012R0000	1SET111010R0000	EK2.5-4P 1SNK705912R0000	2	1SNK905302R0000
	2.5 / 14	0.205	20A		o-ç	ZK2.5-4P-BL	1SNK705022R0000	1SET111029R0000		3	1SNK905303R0000
	4 / 12	0.205	300 A/1s 396 A/1s		o-ç	ZK2.5-PE-4P	1SNK705152R0000			5	1SNK905305R0000
	4 / -	6 /	32A		ð	ZK4-4P	1SNK706012R0000	1SET111014R0000	EK2.5-4P 1SNK705912R0000	2	1SNK906302R0000
	4 / 12	0.236	30A		ð	ZK4-4P-BL	1SNK706022R0000	1SET111033R0000		3	1SNK906303R0000
	6 / 10	0.236	480 A/1s 636 A/1s		o-ç	ZK4-PE-4P	1SNK706152R0000			5	1SNK906305R0000
ð	2.5 / -	5.2 /	24A		& ð	ZK2.5-D2	1SNK705210R0000	1SET111010R0000	EK2.5-D2 1SNK705960R0000	2	1SNK905302R0000
	2.5 / 14	0.205	20A		o-ç	ZK2.5-D2-BL	1SNK705220R0000	1SET111029R0000		3	1SNK905303R0000
	4 / 12	0.205	20A		o-ç	ZK2.5-D1	1SNK705211R0000			5	1SNK905305R0000
60	2.5 / -	5.2 /	22A		ð	ZK2.5-T3	1SNK705510R0000	1SET111010R0000	EK2.5-T3 1SNK705961R0000	2	1SNK905302R0000
	2.5 / 14	0.205	20A		ð	ZK2.5-T1	1SNK705511R0000	1SET111029R0000		3	1SNK905303R0000
	4 / 12	0.205	20A		ð	ZK2.5-T1	1SNK705511R0000			5	1SNK905305R0000
	2.5 / -	5.2 /	22A		o-ç	ZK2.5-L-L-PE	1SNK705512R0000	1SET111010R0000	EK2.5-T3 1SNK705961R0000	2	1SNK905302R0000
	2.5 / 14	0.205	20A		o-ç	ZK2.5-L-N-PE	1SNK705513R0000	1SET111029R0000		3	1SNK905303R0000
	4 / 12	0.205	20A		o-ç	ZK2.5-T1-PE	1SNK705550R0000			5	1SNK905305R0000
3U	2.5 / -	5.2 /	20A		ð	ZK2.5-S	1SNK705310R0000	1SET111010R0000	EK2.5-3P 1SNK705911R0000	2	1SNK905302R0000
	2.5 / 14	0.205	20A		ð	ZK2.5-S	1SNK705310R0000	1SET111029R0000		3	1SNK905303R0000
	4 / 12	0.205	20A		ð	ZK2.5-S	1SNK705310R0000			5	1SNK905305R0000
KJ	2.5 / -	6 /	6.3A		ð	ZK2.5-SF	1SNK706410R0000	1SET111010R0000	EK2.5-3P 1SNK705911R0000	2	1SNK906302R0000
	2.5 / 14	0.236	16A		ð	ZK2.5-SF	1SNK706410R0000	1SET111029R0000		3	1SNK906303R0000
	4 / 12	0.236	16A		ð	ZK2.5-SF-R1	1SNK706411R0000			5	1SNK906305R0000
30Ç	5.2 / 0.205	ð				BAZ1	1SNK900002R0000				
	10 / 0.394	ð				BAM4	1SNK900001R0000				
	10 / 0.394	ð				BAZH1	1SNK900102R0000				
M4	4.8 / 0.189	ð	1->10 (x10)			MC512PA	1SNK140011R0000				
		ð	1->100				1SNK145011R0000				
		Q	1->10 (x10)				1SNK140012R0000				
	5.6 / 0.220	ð	1->10 (x10)			MC612PA	1SNK145012R0000				
		ð	1->100				1SNK150011R0000				
		Q	1->10 (x10)				1SNK155011R0000				
		Q	1->100			1SNK150012R0000					
		Q	1->100			1SNK155012R0000					

