


REVISIONS			
REV	DATE	BY	APP'D
F	14JUL2023	AFK	MIN
A	INITIAL DRAWING		



Product Size	2 (4.8)	3 (6.4)	4 (9.5)	5 (12.7)	6 (19.0)	7 (25.4)	8 (38.1)
Overall Product Thickness (Puffiness)	1.00 to 1.40 [.039] to [.055]	1.20 to 1.60 [.047 to .063]	1.20 to 1.60 [.047 to .063]	1.20 to 1.60 [.047 to .063]	1.20 to 1.80 [.047 to .071]	1.20 to 1.80 [.047 to .071]	1.20 to 1.80 [.047 to .071]
Maximum Recovered I.D.	2.40 [.094]	3.20 [.126]	4.80 [.189]	6.40 [.252]	9.52 [.375]	12.7 [.500]	19.05 [.750]
Recovered Wall Thickness	0.25±0.05 [.010±.002]	0.30±0.08 [.012±.003]	0.30±0.08 [.012±.003]	0.30±0.08 [.012±.003]	0.43±0.08 [.017±.003]	0.48±0.08 [.019±.003]	0.51±0.08 [.020±.003]
Minimum Supplied I.D.	4.80 [.189]	6.40 [.252]	9.50 [.374]	12.7 [.500]	19.0 [.748]	25.4 [1.00]	38.0 [1.496]
Nominal Expanded Wall	0.23 [.009]	0.23 [.009]	0.23 [.009]	0.23 [.009]	0.23 [.009]	0.23 [.009]	0.23 [.009]
Spool Length (m)	50	50	50	50	50	50	50

- NOTES:
1. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES]
  2. ONE SPICE PER SPOOL PERMITTED. BOX IS MARKED WHERE APPLICABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DATE	14APR2023	BY	A. F. KEAN
CHK	14APR2023	APP'D	A. F. KEAN
REV	14JUL2023	DATE	14JUL2023
DESCRIPTION	TMS-CCUV-CT OUTSIDE PRINTER		
SIZE	A2	DATE CODE	01986
SCALE	NTS	DRAWING NO	MCD170021
SHEET	1	REV	A

**STE** TE Connectivity

RESTRICTED TO CUSTOMER DRAWING

MCD170021