



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	01JUN2023	BDA	MB

PART AS SUPPLIED



PART FULLY RECOVERED



PRODUCT DIMENSIONS

ORDERING DESCRIPTION	AS SUPPLIED		AS RECOVERED					
	MINIMUM EXPANDED I.D. (D)		MAXIMUM JACKET RECOVERED (d)		MINIMUM OUTER JACKET WALL THICKNESS AFTER RECOVERY (W)		TOTAL WALL THICKNESS AFTER RECOVERY (WI)	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.
RBK-RTP-125-NR500-COL	11.00	0.433	3.45	0.136	0.70	0.028	1.40	0.055
RBK-RTP-125-NR3-COL	11.00	0.433	4.65	0.183	0.80	0.031	1.80	0.071
RBK-RTP-125-NR5-COL	20.20	0.795	11.40	0.449	1.25	0.049	2.31	0.091

PRODUCT INFORMATION


- OUTER JACKET: IRRADIATED MODIFIED POLYOLEFIN TYPE, COLOURS: BLACK, RED, WHITE, YELLOW
INNER LINER: THERMOPLASTIC HOT-MELT ADHESIVE, COLOUR: LIGHT AMBER
- SHRINK RATIO: 4:1
- FULLY RECOVERED LONGITUDINAL SHRINKAGE 0 TO -12% (NR3 AND NR500)
0 TO -10% (NR5)
- TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING
- THE WALL THICKNESS OF THE TUBING WILL BE LESS THAN SPECIFIED IF RECOVERY IS RESTRICTED DURING SHRINKAGE

⁶ NOMINAL VALUES FOR REFERENCE ONLY

STANDARD CUTTING TOLERANCES(mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm(Inches)



MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ±
- 1 PLC ±0.1
- 2 PLC ±0.01
- 3 PLC ±0.001
- 4 PLC ±0.0001
- ANGLES ±
- FINISH -

DWN 01JUN2023
BASAVARAJA D A

CHK 01JUN2023
SELVAPANDIAN B

APVD 01JUN2023
MAYO BAKARE

PRODUCT SPEC
RK-6764

APPLICATION SPEC

WEIGHT -
CUSTOMER DRAWING



NAME
RBK-RTP-125-NR SIZES

SIZE A3 CAGE CODE - DRAWING NO. C-RBK-RTP-125 RESTRICTED TO -

SCALE NTS SHEET 1 OF 1 REV A