


REVISIONS

REV.	ECO	DESCRIPTION	DATE	APPROVED
C	0632-03	REDRAWN ADDED ITEM 6	15JUL2003	CC

E-311AAB
 RELAY-OVERVOLTAGE
 WITH TIME DELAY



ALL DIMENSIONS ARE IN INCHES



TE CONNECTIVITY
 175 N. DIAMOND STREET MANSFIELD,
 OHIO 44902

TITLE

RELAY-OVERVOLTAGE
 WITH TIME DELAY

TE P.N.

1616126-8

DWG NO.

E-311AAB

DS DATA SHEET

CAGE CODE
 74063

SCALE
 NONE

SHEET
 1 OF 2

REV
 C


GENERAL SPECIFICATION

TIME		VOLTAGE		CURVE	
SPEC. MIL - STD - 704C					
VOLTAGE	MIN.	TIME	MAX.	TIME	
32.5	.075		.30		
35.0	.062		.16		
40	.046		.091		
45	.029		.061		
50	.012		.045		

TRIP POINT
 CONTACT RATING
 CONTACT ARRANGEMENT
 OPERATE TEMPERATURES
 WEIGHT MAX.
 MAX. VOLTAGE
 CONSTRUCTION

31.5 ±1 VDC
 5 AMP RES
 SPST N.C.
 -55°C TO +71°C
 6 OZ.
 150 V.
 CONTACTS HERMETICALLY SEALED

SCHEMATIC



TE CONNECTIVITY
 175 N. DIAMOND STREET MANSFIELD,
 OHIO 44902

TITLE
 RELAY-OVERVOLTAGE
 WITH TIME DELAY

TE P.N.
 1616126-8

DWG NO.
 E-311AAB

THIRD ANGLE PROJECTION

THIS DRAWING PREPARED
 IN ACCORDANCE WITH
 ANSI/ASMEY14.5M-1982

CAGE CODE
 74063

SCALE
 NONE

SHEET
 2 OF 2

REV
 C