


REVISIONS

REV.	ECO	DESCRIPTION	DATE	APPROVED
A	-	UPDATED CURRENT DATA, ITEM 2 PART NUMBER WAS 37308-20	06APR1984	RSS

QR-50W
RELAY-A.C. CURRENT SENSOR
7.5 AMP, 115VAC



ALL DIMENSIONS ARE IN INCHES



TE CONNECTIVITY
175 N, DIAMOND STREET MANSFIELD,
OHIO 44902

TITLE

RELAY-A.C. CURRENT SENSOR
7.5 AMP, 115VAC

TE P.N.

1616132-4

DWG NO.

QR-50W

DS

DATA SHEET

CAGE CODE
74063

SCALE
NONE


SHEET
1 OF 2

REV
A

GENERAL SPECIFICATION

NOM. OPERATING VOLTAGE	115 VRMS
OPERATING FREQUENCY	325 – 600 HZ
CONTINUOUS CURRENT	7.5 A MAX.
PICKUP CURRENT	4.0 A MAX.
DROPOUT CURRENT	1.0 A MAX.
CONTACT ARRANGEMENT	SPST N.C.
CONTACT RATING. LAMP LOAD	100 MA.
VIBRATION	100'S TO 2000 HZ.
ALTITUDE	50,000 FT.
TEMPERATURE	-55°C TO +85°C
VOLTAGE DROP	.35 V MAX. (L1-L2)
MAX. WEIGHT	4 OZ.

SCHEMATIC



ALL DIMENSIONS ARE IN INCHES



TE CONNECTIVITY
175 N. DIAMOND STREET MANSFIELD,
OHIO 44902

TITLE

RELAY-A.C. CURRENT SENSOR
7.5 AMP, 115VAC

TE P.N.

1616132-4

DWG NO.

QR-50W

DS

DATA SHEET

CAGE CODE
74063

SCALE
NONE

SHEET
2 OF 2

REV
A