

6

5


4

3

2

1

REVISIONS					
REV.	ECR#	ZONE	DESCRIPTION	CHANGED BY/DATE	APPROVED BY/DATE
AA			INITIAL RELEASE	S.J. 5/13/2009	S.J. 5/13/2009
AB	MAN-4188		ADDED MOLDABLE SEALANT TAPE TO M&O. ADDED OVERMOLD STRAIN RELIEF TO CABLE.	K.S. 10-05-10	K.S. 10-05-10
AC	MAN-4318		ADDED THREE NON-STRAIN RELIEF CONFIGURATIONS	K.S. 04-20-11	K.S. 04-20-11
AD	MAN-4439		ADDED NUT TORQUE SPEC	WAL 10/11/2011	
AE	ECO-21-00143		ADDED RJ45-ECS-8-NR CONFIGURATION	S.J. 15MAR21	J.Q. 15MAR21



MOLDABLE SEALANT TAPE (MASTIC TAPE) TO BE USED ON CABLE, BENEATH CRUSH GLAND TO ENSURE IP67 COMPLIANCE

CONFIGURATION TABLE		
MODEL NUMBER	DIMENSION "L"	COMMENTS
RJ45-ECS	305.0 +15.0/-5.0	
RJ45-ECS-4	101.6 +15.0/-5.0	
RJ45-ECS-6	152.4 +15.0/-5.0	
RJ45-ECS-ST	305.0 +15.0/-5.0	W/SHRINK TUBING
RJ45-ECS-NR	305.0 +15.0/-5.0	NO STRAIN RELIEF
RJ45-ECS-4-NR	101.6 +15.0/-5.0	NO STRAIN RELIEF
RJ45-ECS-6-NR	152.4 +15.0/-5.0	NO STRAIN RELIEF
RJ45-ECS-8-NR	203.2 +15.0/-5.0	NO STRAIN RELIEF

Data	10BaseT, 100BaseT and 1000BaseT Networks Cat5e per TIA/EIA 568B ClassD per ISO/IEC 11801
Mechanical	Mating Cycles >500 Positive RJ45 bayonet coupling Cat5 Cable Strain Relief
Material	UV Resistant Nylon 66
Sealing	IP67 (Mastic Tape Should Be Used to Achieve)
Salt Spray	>1000h
Flammability	UL94V0
Thermal Shock	10 cycles -40 to +100 deg C
Temperature Range	-40 deg C to +85 deg C
Installation Hole Dia.	20mm
Nut Torque	6 ± 1 in-lbf

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION - - -
 © Copyright 2022 TE Connectivity Ltd. ALL RIGHTS RESERVED.

MATERIAL: NA	THIRD ANGLE PROJECTION	
FINISH: NA	DO NOT SCALE DRAWING	
APPROVALS	DATE	<p>INTERPRET DIMENSIONING AND TOLERANCING IN ACCORDANCE WITH ASME Y14.5M-2009</p> <p>TOLERANCES UNLESS OTHERWISE SPECIFIED</p> <p>DIMENSIONS ARE IN MILLIMETERS</p> <p>ANGLE: ±30'</p> <p>0 PLACE DECIMAL: ±0.5</p> <p>1 PLACE DECIMAL: ±0.25</p> <p>2 PLACE DECIMAL: ±0.13</p> <p>SURFACE ROUGHNESS 1.6</p>
DRAWN BY: S. JOHNSON	5/13/09	
ELEC. ENG: J. MORROW	5/14/09	
MECH. ENG: K. SEARL	5/14/09	
MFG./OPS: I. CHICKLIS	5/14/09	<p>SIZE: A3</p> <p>DWG. NO.: RJ45-ECSMO</p> <p>REV: AE</p>
SCALE: 1:1		PREVIOUS#
		SHEET 1 OF 1

6

5

4

3

2

1