



LABEL AND LINER DESIGN



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
F1		UL LABEL CHANGE	04JUL2024	GSK	DB

PRESENTATION



All dimensions in mm [Inch]

**OUTSIDE WOUND
LABEL ACROSS: 3
PER ROLL QTY: 1000**

TE PN: CN9929-000

UL-MARKING AND LABELLING SYSTEMS

PGCT2 - Flag Labels, Flag Tags, Wrap-around Labels & Related Products - Component	
PGCT8 - Flag Labels, Flag Tags, Wrap-around Labels & Related Products Certified for Canada - Component	
File: MH65661	Model N°: SBP

TOLERANCES mm [INCH]	
LABEL HEIGHT:	± 0.3 [.012]
LABEL WIDTH:	± 0.3 [.012]
WEB WIDTH:	± 0.8 [.031]
VERTICAL REPEAT:	± 0.8 [.031]*
HORIZONTAL REPEAT:	± 0.8 [.031]*
PRINT POSITIONING:	± 0.8 [.031]*
LEFT MARGIN:	± 0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±
MATERIAL SEE TABLE	FINISH GLOSSY

MATERIAL	CLEAR VINYL
ADHESIVE TYPE	ACRYLIC PERMANENT
LINEAR	WHITE KRAFT
DWN GOPALAKRISHNA HV 20MAR2017	TE Connectivity
CHK D.BURGAT 20MAR2017	
APVD D.BURGAT 20MAR2017	NAME SBP LABEL - WHITE 25.4 x 188.9mm [1.00 x 7.43inch]
PRODUCT SPEC TIDS-211	
APPLICATION SPEC	
WEIGHT 0.667g	SIZE A2
CUSTOMER DRAWING	CAGE CODE 00779
	DRAWING NO C=SBP100743WE1
	RESTRICTED TO
	SCALE NTS
	SHEET 1 OF 1
	REV F1