



P	LTR	DESCRIPTION	DATE	DWN	APVD
F1		UL LABEL CHANGE	05JUL2024	GSK	DB

LABEL AND LINER DESIGN



PRESENTATION



OUTSIDE WOUND LABEL ACROSS: 2 PER ROLL QTY: 1000

All dimensions in mm [Inch]

TE PN: CN9935-000

UL-MARKING AND LABELLING SYSTEMS	
PGCT2 - Flag Labels, Flag Tags, Wrap-around Labels & Related Products - Component	
PGCT8 - Flag Labels, Flag Tags, Wrap-around Labels & Related Products Certified for Canada - Component	
File: MH65661	Model N°: SBP

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
4 PLC ±	
ANGLES ±	
MATERIAL: SEE TABLE	FINISH: GLOSSY

MATERIAL: CLEAR VINYL	ADHESIVE TYPE: ACRYLIC PERMANENT	LINEAR: WHITE KRAFT
DWN: 24FEB2017 CHK: GOPALAKRISHNA_HV D.BURGAT APVD: 24FEB2017 D.BURGAT PRODUCT SPEC: TTDS-211 APPLICATION SPEC:		NAME: SBP LABEL-WHITE-T200 PRINTER 50.8 x 95.3mm [2.00 x 3.75inch]
WEIGHT: 0.673g	SIZE: A2	CAGE CODE: 00779
CUSTOMER DRAWING	SCALE: NTS	SHEET: 1 OF 1
DRAWING NO: SBP200375WE1-T200		RESTRICTED TO: F1