

TYPE 1: TOP ENTRY PG16, DOUBLE SIDE ENTRY 2PG16
类 型 1: 顶出PG16, 双侧出2PG16

PG/M THREAD-3
PG/M螺纹孔-3

PG/M THREAD-2
PG/M螺纹孔-2

PG/M THREAD-1
PG/M螺纹孔-1

143.8

65

50

104

27

50

NOTES:

1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: POWDER COATED
DEGREE OF PROTECTION: IP67 (MATED)

注释:
1. 技术参数:
上壳材料: 铝合金
表面处理: 粉末喷涂
防护等级: IP67(配合)

TYPE 2: TOP ENTRY 2M25
类 型 2: 顶出2M25

TYPE 3: TOP ENTRY 2M25, MINIOUS SCREW
类 型 3: 顶出2M25, 带一字槽螺丝

T1802241616-000	H24BK-TG/TSHC-PG16/2PG16	H24BK HOOD, CENTER LOCKING, TOP ENTRY PG16, DOUBLE SIDE ENTRY 2PG16, POWDER COATED, GREY H24BK上壳, 中部锁定, 顶出PG16, 双侧出2PG16, 灰色粉末喷涂	PG16	PG16	PG16	TYPE-1 类型-1
T1822242225-000	H24BK-TGHC-2M25	H24BK HOOD, CENTER LOCKING, TOP ENTRY 2M25, POWDER COATED, GREY H24BK上壳, 中部锁定, 顶出2M25, 灰色粉末喷涂	-	2M25	-	TYPE-2 类型-2
T1826242225-000	H24BK-TGHC-2M25	H24BK HOOD, CENTER LOCKING, MINUS SCREW, TOP ENTRY 2M25, POWDER COATED, GREY H24BK上壳, 中部锁定, 带一字槽螺丝, 顶出2M25, 灰色粉末喷涂	-	2M25	-	TYPE-3 类型-3
PART NUMBER 料 号	PART DESCRIPTION 成 品 描 述	PG/M THREAD-1 PG/M螺纹孔-1	PG/M THREAD-2 PG/M螺纹孔-2	PG/M THREAD-3 PG/M螺纹孔-3	TYPE 类 型	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

-

DWN
BELL SU
05APR2017

CHK
GINO YAO
05APR2017

APVD
CHRIS WANG
05APR2017

PRODUCT SPEC
108-137276

APPLICATION SPEC
114-137276

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

H24BK-TGHC-PG/M

SIZE
A2

CAGE CODE
-

DRAWING NO
T18XX24XXXX000

RESTRICTED TO

SCALE
1:1

SHEET
1 OF 1

REV
B