

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	02NOV2017	RL	CW
	B	ECR-17-017888	14DEC2017	RL	CW

M4 screw, recommended  
tightening torque 1.2Nm  
M4 螺丝, 推荐锁紧力矩为1.2Nm

4 X M3 screw, recommended  
tightening torque 0.5Nm  
4 X M3 螺丝, 推荐锁紧力矩为0.5Nm

Panel cut out for inserts for  
use without hoods/housings  
不使用防护外壳时芯件的安装开孔图

NOTES:

1. TECHNICAL CHARACTERISTICS:  
INSULATION MATERIAL: PC  
RATED VOLTAGE: 500V  
RATED CURRENT: 16A  
INSULATION RESISTANCE:  $\geq 400M\Omega$   
RATED IMPULSE VOLTAGE: 6KV  
POLLUTION DEGREE: 3  
FLAMMABILITY: UL94V-0  
MATING CYCLES: 500 CYCLES  
WIRE RANGE:  $0.5mm^2 \sim 2.5mm^2$  (AWG20-AWG14)  
CONTACT TYPE: SPRING CLAMP

注释:

1. 技术参数:  
绝缘材料: PC  
额定电压: 500V  
额定电流: 16A  
绝缘电阻:  $\geq 400M\Omega$   
脉冲电压: 6KV  
污染等级: 3  
阻燃等级: UL94V-0  
插拔次数: 500 次  
接线范围:  $0.5mm^2 \sim 2.5mm^2$  (AWG20-AWG14)  
接线类型: 弹片压接

T2040063201-001	HE-006-FS	HE-006 FEMALE INSERT, SPRING CLAMP, NO LOGO HE-006母插, 弹片, 无LOGO
-----------------	-----------	--

PART NUMBER  
料号

PART DESCRIPTION  
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN ROY LIU 02NOV2017

CHK GINO YAO 02NOV2017

APVD CHRIS WANG 02NOV2017

PRODUCT SPEC

108-137044

APPLICATION SPEC

114-137044

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:  
mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

-

FINISH

-

TE Connectivity

NAME  
HE-006-FS

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-T2040063201001 -

SCALE 1:1 SHEET 1 OF 1 REV B

1470-19 (3/13)