

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	05MAR2015	DW	CW
	B	ECR-15-015267	19OCT2015	DW	CW
	B1	ECR-18-010979	22JUL2018	RG	CW
	B2	ECR-19-012251	07SEP2019	WQR	CW

TYPE 1, T2059402201-000
类型 I, T2059402201-000

4X M3 THREAD, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3 螺丝, 推荐拧紧力矩 0.5N.m

M4 THREAD—
RECOMMENDED
TIGHTENING TORQUE
1.2Nm
M4 螺丝, 推荐拧紧力矩 1.2N.m

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
CONTACT TYPE: CRIMP CONTACT
- CONTACTS NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20300X20XX000)

注释:

- 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
接线类型: 冷压接
- 端子需要单独订购。
(订货号参考图面: T20300X20XX000)

PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS

不使用防护外壳时芯件的安装开孔图

T2059402201-000	HEEE-040-F	HEEE-040 FEMALE INSERT WITHOUT TE LOGO HEEE-040 母插 无 TE LOGO	TYPE 1 类型 I
PART NUMBER 料号	DESCRIPTION 描述		TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 06MAR2015 David Wang														
DIMENSIONS: mm		CHK 06MAR2015 Chris Wang			NAME HEEE-040-F WITHOUT LOGO											
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 06MAR2015 Xiang Xu														
<table border="1"> <tr> <td>0 PLC</td> <td>±-</td> </tr> <tr> <td>1 PLC</td> <td>±-</td> </tr> <tr> <td>2 PLC</td> <td>±-</td> </tr> <tr> <td>3 PLC</td> <td>±-</td> </tr> <tr> <td>4 PLC</td> <td>±-</td> </tr> <tr> <td>ANGLES</td> <td>±-</td> </tr> <tr> <td>FINISH</td> <td>±-</td> </tr> </table>		0 PLC			±-	1 PLC	±-	2 PLC	±-	3 PLC	±-	4 PLC	±-	ANGLES	±-	FINISH
0 PLC	±-															
1 PLC	±-															
2 PLC	±-															
3 PLC	±-															
4 PLC	±-															
ANGLES	±-															
FINISH	±-															
MATERIAL	-	APPLICATION SPEC 114-137068	SIZE A3	CAGE CODE 00779	DRAWING NO T2059402201000	RESTRICTED TO -										
Customer Drawing			SCALE 1:1	SHEET 1 OF 2	REV B2											

1470-19 (3/13)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

NOTES:
SPEC REFER TO SHEET 1.

注释:
产品规范参照SHEET 1.

TYPE 2, T2059402201-001
类型2, T2059402201-001

M4 THREAD
RECOMMENDED
TIGHTENING TORQUE
1.2Nm
M4 螺丝, 推荐拧紧力矩1.2N.m

4X M3 THREAD, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3 螺丝, 推荐拧紧力矩0.5N.m

T2059402201-001	HEEE-040-F	HEEE-040 FEMALE INSERT WITHOUT LOGO HEEE-040 母插 无 LOGO	TYPE 2 类型 2
PART NUMBER 料号	DESCRIPTION 描述	TYPE 类型	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 06MAR2015		
DIMENSIONS: mm		CHK Chris Wang 06MAR2015		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Xiang Xu 06MAR2015	NAME HEEE-040-F WITHOUT LOGO	
0 PLC ±-		PRODUCT SPEC 108-137068	SIZE A3	
1 PLC ±-		APPLICATION SPEC 114-137068	CAGE CODE 00779	DRAWING NO T2059402201000
2 PLC ±-		WEIGHT -	RESTRICTED TO -	
3 PLC ±-		Customer Drawing		
4 PLC ±-		SCALE 1:1		
ANGLES ±-		SHEET 2 OF 2		
FINISH		REV B2		

1470-19 (3/13)