

# MC512PA G (x100) Vertical



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Markers and Marking Systems  
→ Terminal Block Markers

## General Information

|                               |   |
|-------------------------------|---|
| <b>Extended Product Type:</b> | MC512PA G (x100) Vertical                                       |
| <b>Product ID:</b>            | 1SNK146072R0000   |
| <b>EAN:</b>                   | 3472599999572   |
| <b>Catalog Description:</b>   | MC512PA Terminal Block Markers pre-printed : G (x100) Vertical  |
| <b>Long Description:</b>      | MC512PA Terminal Block Markers pre-printed : G (x100) Vertical. |

## Ordering

|                                |          |
|--------------------------------|----------|
| <b>Color:</b>                  | White    |
| <b>Minimum Order Quantity:</b> | 1 piece  |
| <b>Customs Tariff Number:</b>  | 39269097 |

## Popular Downloads

|   |                 |
|---|-----------------|
| <b>Data Sheet, Technical Information:</b> | 1SNK160005D0201 |
| <b>Instructions and Manuals:</b>          | 1SNK160027C0201 |

## Dimensions

|                                    |        |
|------------------------------------|--------|
| <b>Product Net Width:</b>          | 5.2 mm |
| <b>Product Net Height:</b>         | 12 mm  |
| <b>Product Net Length:</b>         | 5 mm   |
| <b>Product Net Depth / Length:</b> | 4.8 mm |
| <b>Product Net Weight:</b>         | 10 g   |

## Technical

|                              |  |
|------------------------------|--|
| <b>Spacing:</b>              | 5.2 mm   |
| <b>Function:</b>             | Pre-printed marker card                                      |
| <b>Degree of Protection:</b> | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| <b>Insulation Material:</b>  | Polyamide  |

## Technical UL/CSA

|  |    |
|--|----|
| <b>Flammability According to UL94:</b> | V2 |
|--|----|

## Environmental

|                                 |  |
|---------------------------------|--|
| <b>Ambient Air Temperature:</b> | Operation -55 ... +110 °C<br>Storage -55 ... +110 °C |
|---------------------------------|--|

|                     |   |
|---------------------|---|
| <b>RoHS Status:</b> | Following EU Directive 2002/95/EC August 18, 2005 and amendment |
|---------------------|---|

## Certificates and Declarations (Document Number)

|  |                 |
|--|-----------------|
| <b>Declaration of Conformity - CE:</b> | 1SND225156C1000 |
| <b>Environmental Information:</b>      | 1SND220060E1000 |
| <b>Instructions and Manuals:</b>       | 1SNK160027C0201 |
| <b>RoHS Information:</b>               | 1SND230504F0204 |

## Classifications

|                                    |   |
|------------------------------------|---|
| <b>Object Classification Code:</b> | X                                       |
| <b>E-number:</b>                   | 2967481                                 |
| <b>ETIM 4:</b>                     | EC000761 - Labelling for terminal block |
| <b>ETIM 5:</b>                     | EC000761 - Labelling for terminal block |
| <b>ETIM 6:</b>                     | EC000761 - Labelling for terminal block |

## Container Information

|  |               |
|--|---------------|
| <b>Package Level 1 Units:</b>          | 1 piece       |
| <b>Package Level 1 Width:</b>          | 120 mm        |
| <b>Package Level 1 Depth / Length:</b> | 200 mm        |
| <b>Package Level 1 Gross Weight:</b>   | 0.01 kg       |
| <b>Package Level 1 EAN:</b>            | 3472599999572 |
| <b>Package Level 2 Units:</b>          | 600 piece     |
| <b>Package Level 2 Gross Weight:</b>   | 6 kg          |
| <b>Package Level 3 Units:</b>          | 14400 piece   |

