

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	05MAR2015	DW	CW
	B	ECR-15-015267	20OCT2015	DW	CW
	BI	ECR-19-012251	09SEP2019	WQR	CW

M4 THREAD, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4 螺丝, 推荐拧紧力矩 1.2N.m

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
CONTACT TYPE: CRIMP CONTACT

2. CONTACTS NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20300X20XX000)

4X M3 THREAD, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3 螺丝, 推荐拧紧力矩 0.5N.m

PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS
不使用防护外壳时芯件的安装开孔图

注释:

1. 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
接线类型: 冷压接

2. 端子需要单独订购.
(订货号参考图面: T20300X20XX000)

T2059722201-000	HEEE-072-F	HEEE-072 FEMALE INSERT, NO LOGO HEEE-072母插, 无LOGO
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05MAR2015 David Wang	TE Connectivity NAME HEEE-072 FEMALE INSERT, NO LOGO				
DIMENSIONS: mm		CHK 05MAR2015 Chris Wang					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 05MAR2015 Xiang Xu					
0 PLC \pm 1 PLC \pm 2 PLC \pm 3 PLC \pm 4 PLC \pm ANGLES \pm		PRODUCT SPEC 108-137068					
MATERIAL		APPLICATION SPEC 114-137068	SIZE A3	CAGE CODE 00779	DRAWING NO T2059722201000	RESTRICTED TO -	
-		WEIGHT -	SCALE 1:1		SHEET 1	OF 1	REV BI
-		Customer Drawing					

1470-19 (3/13)