



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	05JUN2018	CD	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
SHELL MATERIAL: NICKEL PLATED BRASS
SEAL MATERIAL: ELASTIC RUBBER
PINCH RING MATERIAL: PA
OPERATION TEMPERATURE: -40°C-+100°C
PROTECTION DEGREE: IP68
WIRE RANGE: 7-12MM

技术指标:
1. 技术参数:
主体材料: 铜镀镍
密封材料: 弹性橡胶
夹紧件材料: PA
工作温度: -40°C-+100°C
防护等级: IP68
夹线范围: 7-12MM



T3609162711000	DLX-27-MTS	METAL CABLE GLAND M27 (7-12) 金属接头 M27 (7-12)
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05JUN2018 CHARLLIAN DENG	TE Connectivity DLX-27-MTS		
DIMENSIONS: mm		CHK 05JUN2018 GINO YAO			
		APVD 05JUN2018 CHRIS WANG			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC	NAME		
MATERIAL		FINISH	SIZE	CAGE CODE	DRAWING NO
-		-	A3	00779	©-T3609162711000
-		-	RESTRICTED TO		
CUSTOMER DRAWING			SCALE	SHEET	REV
			2:1	1 OF 1	A