



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	04MAR2024	AN	VN



PRODUCT DIMENSIONS

SIZE	AS SUPPLIED		AS RECOVERED			
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		WALL THICKNESS AFTER RECOVERY (W)	
	mm.	in.	mm.	in.	mm.	in.
13.5/4.5	13.50	0.531	4.50	0.177	1.50±0.35	0.059±0.014


PRODUCT INFORMATION

- NON-FLAME RETARDANT
- OUTER JACKET: SEMI CONDUCTIVE IRRADIATED MODIFIED POLYOLEFIN
COLOUR: BLACK
INNER LINER: SEMI CONDUCTIVE HOT MELT ADHESIVE
COLOUR: BLACK
- SHRINK RATIO 3:1
- LONGITUDINAL CHANGE 0 TO -10%
- TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±:
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±:
FINISH -

DWN	04MAR2024
AYESHABANU N	
CHK	04MAR2024
BASAVARAJA D A	
APVD	04MAR2024
VLADIMIR NEMEC	
PRODUCT SPEC	RW-2080
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	



NAME
TECT-DUAL WALL SLEEVING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	TECT	-
SCALE	NTS	SHEET	1 OF 1
REV	A		