



CIRCUIT DIAGRAM



Dustproof:  
 Protection class IP 54 acc. to IEC 529 (EN 60529)  
 All plug-terminals  
 Terminals shape similar to ISO 8092-1  
 Coil and Load Terminals 6.3 mm ± 0.1 mm x 0.8 mm ± 0.05 mm  
 Integrated component: Resistor 680 Ohm

PART	MATERIAL	COLOUR
Cover	PA 66 GF 25	Black sim. to RAL 9005
Base	PA 66 GF 25	Black sim. to RAL 9005
Coil Terminals 85 and 86	CuSn	Pre-tinned Sn
Load Terminals 30 and 87	E-Cu	Pre-tinned Sn

Nominal Voltage: 12 V  
 Coil Resistance: 91 Ohm ± 10% at 23° C  
 Equivalent Resistance: 80,3 Ohm ± 10% at 23° C

1) At Base level.

PART NUMBER	REV	TE PART NAME	COUNTRY OF ORIGIN
1-1414099-0	A	V23134B0052X270	Portugal
7-1904094-1	A		China

PROPRIETARY  
 THE REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR IT'S CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES. ALL RIGHTS, INCLUDING RIGHTS CREATED BY REGISTERED PATENT(S) GRANTED FOR A UTILITY MODEL OR DESIGN, ARE RESERVED.

CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD

PAPER SIZE: A2

APPLICABLE SPEC.: FINISH

DIMENSIONS APPLY PLATING

SCALE: 1:1; 2:1 WEIGHT

MATERIAL

PART NAME: POWER F Relay Normally Open

REV.	CHANGE ORDER	DATE	APP.	DATE	NAME	PART NAME	DWG NO.	SHT. OF 1
				07FEB2013	L.Sandoval	POWER F Relay Normally Open	C- V23134-B0052-X270	1
CI	ECN-22-140797	24FEB2022	L.Sand					
C	ECO-15-016858	23NOV2015	L.Sand					
BI	ECO-14-015632	14OCT2014	L.Sand					
B	ECR-14-010119	04JUL2014	L.Sand					
A	Initial Release	07FEB2013	L.Sand					

CUSTOMER DRAWING

