



Engineering Product Design

Product Construction
120 Conductor Cable
Shielded and Jacketed

Controlled Customer Copy
B.W.B.
GERMANY

Product Description
VG 95218 T028 C030

Rev
2

Designer
Paul Cleary



Date
10/12/2020

Product Manager
Mark Johnstone

Date
10/12/2020

Component Identification

Cross-Section



Components

ID	Type	Quantity	Part Description
A	Cable	60	VG 95218-T021-C034

Component Identification

Key	Wire/Core Colour(s)	Wire/Core Number(s)	Jacket/Wrap Colour(s)	Jacket/Wrap Number
A1	9/9	1/2		
A2	9/9	3/4		
A3	9/9	5/6		
A4	9/9	7/8		
A5	9/9	9/10		
A6	9/9	11/12		
A7	9/9	13/14		
A8	9/9	15/16		
A9	9/9	17/18		
A10	9/9	19/20		
A11	9/9	21/22		
A12	9/9	23/24		



Engineering Product Design

Product Construction 120 Conductor Cable Shielded and Jacketed	Controlled Customer Copy B.W.B. GERMANY	Product Description VG 95218 T028 C030	Rev 2
---	--	---	-----------------

Component Identification

Key	Wire/Core Colour(s)	Wire/Core Number(s)	Jacket/Wrap Colour(s)	Jacket/Wrap Number
A13	9/9	25/26		
A14	9/9	27/28		
A15	9/9	29/30		
A16	9/9	31/32		
A17	9/9	33/34		
A18	9/9	35/36		
A19	9/9	37/38		
A20	9/9	39/40		
A21	9/9	41/42		
A22	9/9	43/44		
A23	9/9	45/46		
A24	9/9	47/48		
A25	9/9	49/50		
A26	9/9	51/52		
A27	9/9	53/54		
A28	9/9	55/56		
A29	9/9	57/58		
A30	9/9	59/60		
A31	9/9	61/62		
A32	9/9	63/64		
A33	9/9	65/66		
A34	9/9	67/68		
A35	9/9	69/70		
A36	9/9	71/72		
A37	9/9	73/74		
A38	9/9	75/76		
A39	9/9	77/78		
A40	9/9	79/80		
A41	9/9	81/82		
A42	9/9	83/84		
A43	9/9	85/86		
A44	9/9	87/88		
A45	9/9	89/90		
A46	9/9	91/92		
A47	9/9	93/94		
A48	9/9	95/96		
A49	9/9	97/98		
A50	9/9	99/100		



Engineering Product Design

Product Construction 120 Conductor Cable Shielded and Jacketed	Controlled Customer Copy B.W.B. GERMANY	Product Description VG 95218 T028 C030	Rev 2
---	--	---	-----------------

Component Identification

Key	Wire/Core Colour(s)	Wire/Core Number(s)	Jacket/Wrap Colour(s)	Jacket/Wrap Number
A51	9/9	101/102		
A52	9/9	103/104		
A53	9/9	105/106		
A54	9/9	107/108		
A55	9/9	109/110		
A56	9/9	111/112		
A57	9/9	113/114		
A58	9/9	115/116		
A59	9/9	117/118		
A60	9/9	119/120		

Cabling

Layer No	Quantity	Description	Nominal O.D. mm
Layer 1	1	Filler	
Layer 2	6	VG 95218-T021-C034	
Layer 3	12	VG 95218-T021-C034	
Layer 4	18	VG 95218-T021-C034	
Layer 5	24	VG 95218-T021-C034	16.2

Outer

Layer Type	Description	Nominal O.D. mm
Wrap:	Polyester	16.3
Shield: Optimised Braid	Tin Plated Copper	17.2
Jacket: Extrusion 1	Zerohal® - Black Marked 'Raychem - VG 95218 T028 C030 - K1010 - VDE Reg.Nr. 7095'	19.6 ±0.5 Min Wall - 1.00mm

Cable Characteristics

Calculated Maximum Weight	582 (kg/km)
Maximum Surface Transfer Impedance	50 milli Ohms/metre @ 30MHz 30 milli Ohms/metre @ 10MHz
This cable is RoHS Compliant	

Specifications

VG 95218 Part 28 Type C



Engineering Product Design

Product Construction 120 Conductor Cable Shielded and Jacketed	Controlled Customer Copy B.W.B. GERMANY	Product Description VG 95218 T028 C030	Rev 2
---	--	---	-----------------

Notes

Braid - AWG 32
Internal reference - EPD93747B

Lengths

Unless otherwise specified on your order this cable may be supplied in the following maximum number of continuous lengths with no single length less than 25m:

Order Quantity (m) + One other length
100

Tyco Electronics UK Ltd.
Faraday Road, Dorcan
Swindon
SN3 5HH
Tel: (01793) 528171
Website: www.te.com

TE Connectivity is a trading name
of Tyco Electronics UK Ltd, which
is registered in England and
Wales, number 550926.
Registered office: Faraday Road,
Dorcan, Swindon, SN3 5HH

This drawing and the information set forth hereon
are the property of Tyco Electronics UK Ltd, and
are to be held in trust and confidence. Publication,
duplication, disclosure or use for any purpose not
expressly authorised in writing by Tyco Electronics
UK Ltd is prohibited.

© 2020 Tyco Electronics UK Limited.
A TE Connectivity Ltd company.
All Rights Reserved.