




Connectors > Automotive Connectors > Automotive Housings



Connector System: **Wire-to-Wire**

Number of Positions: **13**

Connector & Housing Type: **Receptacle**

Centerline (Pitch): **4.8 mm [ .189 in ]**

Sealable: **Yes**

## Features

### Product Type Features

Mixed & Hybrid Connector	No
Connector System	Wire-to-Wire
Connector & Housing Type	Receptacle
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	On the Terminal

### Configuration Features

Number of Positions	13
Number of Rows	3

### Body Features

Primary Product Color	White
-----------------------	-------

### Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

### Housing Features

Centerline (Pitch)	4.8 mm[.189 in]
--------------------	-----------------

## Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: DEC 2010 (44) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Customers Also Bought



TE Part #1745072-2  
15 WAY MCP 2.8 SEALED  
CONNECTOR




TE Part #284802-2  
6POS MQS REC COD B



TE Part #HDP24-18-14PE-L015  
REC, 14P, BLK, E, THD, 16, P



TE Part #2377780-1  
36POS,AMP MCP 1.5K,REC HSG ASSY,  
UNSLD



TE Part #282706-1  
ECONOSEAL J DOUBLE-LOCK 3 WAY



TE Part #4-1633132-7  
ANVIL, COMBINATION .090



TE Part #2500034-4  
SRC Female Conduit Cover



TE Part #1-2500034-6  
SRC Female Conduit Cover



TE Part #1-344273-1  
3 WAY REC. HSG. NBR. SEALECONO



TE Part #281856-2  
POSITIVE LOCK HOUSING

## Documents

### Product Drawings

13 WAY REC HSG. NBR. SEALECONO

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_1-344263-2\\_J.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1-344263-2\\_J.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1-344263-2\\_J.2d\\_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.