

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNK Series

General Information

Extended Product Type:	ZK2.5-D2-PE
Product ID:	1SNK705212R0000
EAN:	3472597052125
Catalog Description:	ZK2.5-D2-PE PI-Spring Clamp Terminal Block - Double Deck - Grey, Green / Yellow
Long Description:	Combine high performance with compact dimensions: - 800 V IEC 600 V U L, - 1 feed through circuit and 1 ground circuit in just 5.2 mm 0.205 in spacing, - 2 jumper channels and a large input and output marker zone on each deck, - designed for easy wiring.

Ordering

Color:	Grey, Green-Yellow
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK162038D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	5.2 mm
Product Net Height:	84.6 mm
Product Net Length:	60.3 mm
Product Net Depth / Length:	60.3 mm
Product Net Weight:	15.7 g

Technical

Rated Cross-Section:	2.5 mm ²
Spacing:	5.2 mm
Connection Type:	PI Spring
Function:	Feed-through + Ground
Number of Levels:	2
Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.22 ... 2.5 mm ² Spring Clamp / Rigid 1x 0.2 ... 4 mm ² Spring Clamp / With Insulated Ferrule 1x 0.22 ... 2.5 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.22 ... 2.5 mm ² Spring Clamp / With Twin Ferrule 2x 0.22 ... 0.5 mm ²

Gauge Type:	A2 / 2.3 mm Dia.
Rated Current (I_n):	Main Circuit 24 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 300 A
Rated Voltage (U_r):	800 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Pollution Degree:	3
Power Loss:	0.8 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	11.0 mm

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Rigid 1x 26 ... 12 AWG Spring Clamp / With Insulated Ferrule 1x 26 ... 14 AWG Spring Clamp / Without Insulated Ferrule 1x 26 ... 14 AWG
Connecting Capacity UL/CSA:	Stranded 12 AWG
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

ATEX Certificate:	1SND162009A1702
BV Certificate:	1SND162013A0203
CB Certificate:	1SND162022A0200
CSA Certificate:	1SND162014A0206
cUL Certificate:	1SND162012A0204
Declaration of Conformity - CE:	1SND225112U1004
DNV Certificate:	1SND162023A0200
EAC Certificate:	1SND161010A1100
Environmental Information:	1SND220072E1002

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230535F0201

Classifications

Object Classification Code: X

ETIM 4: EC000897 - Feed-through terminal block

ETIM 5: EC000897 - Feed-through terminal block

ETIM 6: EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units: 20 piece

Package Level 1 Width: 86 mm

Package Level 1 Depth / Length: 106 mm

Package Level 1 Height: 62 mm

Package Level 1 Gross Weight: 0.334 kg

Package Level 1 EAN: 3472597052125

Package Level 2 Units: 320 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 400 mm

Package Level 2 Height: 200 mm

Package Level 2 Gross Weight: 5.344 kg

Package Level 3 Units: 15360 piece

Product Packing Type: Box

