

ZK2.5-T1-PE



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNK Series

General Information

Extended Product Type:	ZK2.5-T1-PE
Product ID:	1SNK705550R0000
EAN:	3472599854222
Catalog Description:	ZK2.5-T1-PE PI-Spring clamp Terminal Block - Triple Deck - Ground with 6 connections - Green-Yellow
Long Description:	Improve the safety of your installation in the event of a short-circuit thanks to our screwless rail contact: - Rail contact non operator dependent, - Performances above the requirements of the IEC 60947-7-2 terminal block standard, - Secured snap on or off the rail, - Profile aligned with ZK2.5-T3, - 1 jumper channel on bottom and middle decks.

Ordering

Color:	Green-Yellow
---------------	--------------

Minimum Order Quantity:	25 piece
--------------------------------	----------

Customs Tariff Number:	85369010
-------------------------------	----------

Popular Downloads

Data Sheet, Technical Information:	1SNK162062D0201
-------------------------------------------	-----------------

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

Dimensions

Product Net Width:	5.2 mm
---------------------------	--------

Product Net Height:	101.9 mm
----------------------------	----------

Product Net Depth / Length:	73.3 mm
------------------------------------	---------

Product Net Weight:	21.53 g
----------------------------	---------

Technical

Rated Cross-Section:	2.5 mm ²
-----------------------------	---------------------

Spacing:	5.2 mm
-----------------	--------

Connection Type:	PI Spring
-------------------------	-----------

Function:	Ground
------------------	--------

Number of Levels:	3
--------------------------	---

Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.22 ... 2.5 mm ² Spring Clamp / Rigid 1x 0.2 ... 4 mm ² Spring Clamp / With Insulated Ferrule 1x 0.22 ... 2.5 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.22 ... 2.5 mm ² Spring Clamp / With Twin Ferrule 2x 0.22 ... 0.5 mm ²
------------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Gauge Type:	A2 / 2.3 mm Dia.
Rated Short-time Withstand Current (I_{cw}):	for 1 s 300 A
Dielectric Test Voltage:	2000 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Technical UL/CSA

Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Rigid 1x 26 ... 12 AWG Spring Clamp / With Insulated Ferrule 1x 26 ... 14 AWG Spring Clamp / Without Insulated Ferrule 1x 26 ... 14 AWG
Connecting Capacity UL/CSA:	Stranded 12 AWG
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

ATEX Certificate:	1SND162009A1702
BV Certificate:	1SND162013A0203
CB Certificate:	1SND162026A0200
CSA Certificate:	1SND162014A0206
cUL Certificate:	1SND162012A0204
Declaration of Conformity - CE:	1SND225112U1004
EAC Certificate:	1SND162001A1100
Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230535F0202

Classifications

Object Classification Code:	X
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units: 25 piece

Package Level 1 Width: 117 mm

Package Level 1 Depth / Length: 147 mm

Package Level 1 Height: 97 mm

Package Level 1 Gross Weight: 0.538 kg

Package Level 1 EAN: 3472599854222

Package Level 2 Units: 350 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 500 mm

Package Level 2 Height: 300 mm

Package Level 2 Gross Weight: 7.536 kg

Package Level 3 Units: 8400 piece

Product Packing Type: Box

