

## **Type CRG Series**

### **Key Features**

Thick Film
Resistors with
high power to
size ratio,
ideally suited
to industrial
and general
purpose use

Value range from  $1\Omega$  to  $10M\Omega$ 

Eight package sizes

Terminal finish matte Sn over Ni



The resistive element is screen printed and fired, and a passivation layer added. Each resistor is trimmed to tolerance by laser. The pre-scribed tile is then broke into strips, the end plating fired on, and the strips broken into individual components. Final termination finish is electroplated matte Sn over a Ni barrier layer.

#### **Electrical Characteristics**


Туре		0201	0402	0603	0805	1206	1210	2010	2512		
Power ratin	Power rating (W)		0.0625	0.1	0.125	0.25	0.5	0.75W	1W		
Resistance	Min	1R0	1R0	1R0	1R0	1R0	1R0	1R0	1R0		
range (Ω)	Max	10M	10M	10M	10M	10M	10M	10M	10M		
Selection	E24		AVAILABLE AS STANDARD								
Series	E96				ON APF	PLICATIO	N				
Tolerance (9	Tolerance (%)		1	1	1	1	1	1	1		
Code Letter	Code Letter		F	F	F	F	F	F	F		
Max Workir	Max Working Voltage		50V	75V	150V	200V	200V	200V	200V		
Max Overlo	ad Voltage	50V	100V	150V	300V	400V	500V	500V	500V		
Dielectric St	rength (V)	-	100V	300V	500V	500V	500V	500V	500V		
Rated current (Jumper) (A)		0.5A	1A	1A	2A	2A	2A	2A	2A		
	Max Overload Current (Jumper) (A)		2A	2A	5A	10A	10A	10A	10A		
Temperatur	e Range			•	-55°C	~ 155°C	,	•	•		

#### Power rating:


Resistors shall have a power rating based on continuous load operation at an ambient temperature of 70  $^{\circ}\text{C}$  . For temperature in excess of 70  $^{\circ}\text{C}$  , The load shall be derate as shown below




## **Derating Chart**



### Constuction



#### **Dimensions:**



Tuno		[	Dimensions (mm	)	
Type	L	W	Н	<i>l</i> 1	ℓ2
0201	0.60±0.03	0.30±0.03	0.23±0.03	0.10±0.05	0.15±0.05
0402	1.00±0.10	0.50±0.05	0.35±0.05	0.20±0.10	0.25±0.10
0603	1.60±0.10	0.80+0.15	0.45±0.10	0.30±0.20	0.30±0.20
		-0.10			
0805	2.00±0.15	1.25+0.15	0.55±0.10	0.40±0.20	0.40±0.20
		-0.10			
1206	3.10±0.15	1.55+0.15	0.55±0.10	0.45±0.20	0.45±0.20
		-0.10			
1210	3.10±0.10	2.60±0.15	0.55±0.10	0.50±0.25	0.50±0.20
2010	5.00±0.10	2.50±0.15	0.55±0.10	0.60±0.25	0.50±0.20
2512	6.35±0.10	3.20±0.15	0.55±0.10	0.60±0.25	0.50±0.20



# Performance Specification:

Charactarist's	Charification	Tost Mothods
Characteristic	Specification	Test Methods (JIS C 5201-1)
*Insulation	1,000MΩ Min.	Apply 500V DC between protective coating
Resistance	1,00010122 1011111.	and termination for 1 min, then measure
Resistance		(Sub-clause 4.6)
*Dielectric	No evidence of flashover	Apply 100V(0402) 300V(0603) & 500V
Withstanding	mechanical damage, arcing	(0805,1206,1210,2010,2512) AC between
Voltage	or insulation break down	protective coating and termination for 1
		minute (Sub-clause 4.7)
Temperature	1Ω-10Ω : ± 400 PPM/°C	Natural resistance change per temp.
Coefficient of	,	degree centigrade.
Resistance	$10.1\Omega$ - $100\Omega$ : ± 200 PPM/°C	R2-R1
(TCR)		x 10 <sup>6</sup> (PPM/°C)
	101Ω~10MΩ : ± 100 PPM/°C	R1(t2-t1)
		R1: Resistance value at room temperature
	For 0201: >100Ω : ± 200	(t1)
	PPM/°C	R2: Resistance value at room temp. plus
		100 °C (t2)
		(Sub-clause 4.8)
Short Term	Resistance change rate is:	Permanent resistance change after the
Overload	$\pm 5\%$ (2.0% + 0.1 $\Omega$ ) Max.	application of a potential of 2.5 times
	± 1% (1.0% + 0.1Ω) Max.	RCWV for 5 seconds
	,	(Sub-clause 4.13)
*Solderability	95 % coverage Min.	Test temperature of solder : 245 ±3°C
	-	Dipping time solder : 2-3 seconds
		(Sub-clause 4.17)
Soldering	Electrical characteristics	Wave soldering condition: (2 cycles Max.)
Temp.	shall be satisfied without	Pre-heat : 100 ~ 120 °C, 30 ± 5 sec.
Reference	distinct deformation in	Suggestion solder temp.: 235 ~ 255 °C, 10
	appearance.	sec. (Max.)
	(95 % coverage Min.)	Peak temp.: 260 °C
		Reflow soldering condition: (2 cycles
		Max.)
		Pre-heat: 150 ~ 180 °C, 90 ~ 120 sec. Suggestion solder temp.: 235 ~ 255 °C, 20 ~
		40 sec.
		Peak temp.: 260 °C
		(b)
		250 Peak: 260°C (Max)
		200 Pre Heating Zone
		180.0
		150 °C 90 – 120 sec
		100 20~40 sec
		Soldering Zone
		Heating time
		Temperature profile for evaluation  Hand soldering condition:
		The soldering iron tip temperature should
		be less than 300°Cand maximum contract
		time should be 5 sec.
Soldering	Resistance change rate is:	Dip the resistor into a solder bath having a
Heat	±(1%+0.05Ω) Max.	temperature of 260°C±3°C and hold it for
	•	10±1 seconds.
		(Sub-clause 4.18)
		(Sub-clause 4.18)



#### Performance Specification: (Continued)

Characteristic	Specification	Test Methods				
		(JIS C 5201-1)				
Temperature	Resistance change rate is	Resistance cha	ange after contir	nuous		
Cycling		5 cycles for duty cycle specified below:				
	$\pm$ 5% (1.0% + 0.05Ω) Max.	Step Temperature Time				
	$\pm$ 1% (0.5% + 0.05Ω) Max.	1	-55°C±3°C	30 mins		
		2 Room Temp 10~15 r				
		3 155°C±2°C 30 mins				
		4 Room Temp 10~15 m				
		(Sub-clause 4.19)				
Load Life in	Resistance change rate is	Resistance change after 1,000 hours (1.5				
Humidity	$\pm$ 5% (3.0% + 0.1Ω) Max.	hours "on", 0.5 hour "off" ) at RCWV in a				
	$\pm$ 1% (1.0% + 0.1Ω) Max.	humidity chamber controlled at 40°C ± 2°C				
		and 90 to 95 % relative humidity				
		(Sub-clause 4.	24.2.1)			
Load Life	Resistance change rate is	Permanent re	sistance change	after 1,000		
	$\pm$ 5% (3.0% + 0.1Ω) Max.	hours operati	ng at RCWV, wit	h duty cycle		
	$\pm$ 1% (1.0% + 0.1Ω) Max.	of (1.5 hours"	on", 0.5 hour"of	f") at 70°C ±		
		2°C ambient				
		(Sub-clause 4.25.1)				
Terminal	Resistance change rate is	Twist of Test Board :				
Bending	$\pm$ (1.0% + 0.05Ω) Max.	Y/X = 5/90 mr	n for 10 seconds	;		
	(Sub-clause 4.33)					
The resistors of	$\int \Omega \Omega$ only can do the characteris	tic noted of *				

#### **Environment Related Substance**

This product complies to EU RoHS directive, EU PAHs directive, EU PFOS directive and Halogen free. Ozone layer depleting substances are not used in our manufacturing process of this product.

This product is not manufactured using Chloro fluorocarbons (CFCs), Hydrochlorofluorocarbons (HCFCs), Hydrobromofluorocarbons (HBFCs) or other ozone depleting substances in any phase of the manufacturing process.

#### **Storage Condition**

The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of 25°C  $\pm$  10°C and a relative humidity of 60%RH  $\pm$  10%RH, chemical and dust free atmosphere

Even within the above guarantee periods, do not store these products in the following conditions otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

- 1. In salty air or in air with a high concentration of corrosive gas, such as Cl2, H2S, NH3, SO2, or NO2
- 2. In direct sunlight



# Marking

E24 series 0603 – 2512 3 Digits – first two digits denote significant figures of resistance and third digit denotes number of zeros thereafter. EG

Marking for E96 Series 0805 - 2512 4 digits – First three digits denote significant figures of resistance and fourth digit denotes number of zeros thereafter. EG.

For ohmic values below 100R letter "R" denotes decimal point. EG

0201 and 0402 size chips are not marked

0603 E96 3 digit marking.

Resistance Code from table on next page, and Multiplier code from table below

Multiplier Code

Code	Α	В	С	D	E	F	G	Н	Χ	Υ	Z
Mult.	10°	10¹	10 <sup>2</sup>	10³	10 <sup>4</sup>	10 <sup>5</sup>	10 <sup>6</sup>	10 <sup>7</sup>	10 <sup>-1</sup>	10-2	10 <sup>-3</sup>



#### Resistance Code


Value	Code	Value	Code	Value	Code	Value	Code	Value	Code
100	01	162	21	261	41	422	61	681	81
102	02	165	22	267	42	432	62	698	82
105	03	169	23	274	43	442	63	715	83
107	04	174	24	280	44	453	64	732	84
110	05	178	25	287	45	464	65	750	85
113	06	182	26	294	46	475	66	768	86
115	07	187	27	301	47	487	67	787	87
118	08	191	28	309	48	499	68	806	88
121	09	196	29	316	49	511	69	825	89
124	10	200	30	324	50	523	70	845	90
127	11	205	31	332	51	536	71	866	91
130	12	210	32	340	52	549	72	887	92
133	13	215	33	348	53	562	73	909	93
137	14	221	34	357	54	576	74	931	94
140	15	226	35	365	55	590	75	953	95
143	16	232	36	374	56	604	76	976	96
147	17	237	37	383	57	619	77	8	1
150	18	243	38	392	58	634	78		
154	19	249	39	402	59	649	79		
158	20	255	40	412	60	665	80	465	

### Label

Label shall be marked with the following item:

- A. Nominal Resistance and Resistance Tolerance
- B. Power Rating and Size
- C. Quantity and description
- D. Part No.
- E. Lot No.

Ex.







# **Packing Specification:**

Tape dimensions (mm)

## A. Paper Taping




Type	A±0.2	B±0.2	C±0.05	ØD+0.1	E±0.1	F±0.05	G±0.1	W±0.2	T±0.1
				-0					
0201	0.40	0.70	2.0	1 5	1.75	2.5	4.0	8.0	0.42
	±0.05	±0.05	2.0	1.5	1./5	3.5	4.0	8.0	0.42
0402	0.65	1.15	2.0	1.5	1.75	3.5	4.0	8.0	0.45



Type	A±0.2	B±0.2	C±0.05	ØD+0.1	E±0.1	F±0.05	G±0.1	W±0.2	T±0.1
				-0					
0603	1.10	1.90	2.0	1.5	1.75	3.5	4.0	8.0	0.67
0805	1.65	2.40	2.0	1.5	1.75	3.5	4.0	8.0	0.81
1206	2.00	3.60	2.0	1.5	1.75	3.5	4.0	8.0	0.81
1210	2.80	3.50	2.0	1.5	1.75	3.5	4.0	8.0	0.75


#### B. Embossed Taping



Туре	Α	В	С	ØD+0.1	ØD1+0.1	Е	F	G	W	Т
	±0.2	±0.2	±0.05	-0	-0	±0.1	±0.05	±0.1	±0.2	±0.1
2010	2.90	5.60	2.0	1.5	1.5	1.75	5.5	4.0	12.0	1.0
2512	3.50	6.70	2.0	1.5	1.5	1.75	5.5	4.0	12.0	1.0


<sup>\*</sup> Peeling Strength of Top Cover Tape

Test Condition: 0.1 to 0.7 N at a peel-off speed of 300 mm / min.





# Reel Dimension (mm)



Type	Taping	Reel	A ±0.5	B ±0.5	C ±0.5	D±1	M ±1	W ±1
		Quantity						
0201	Papar	10,000	2	13	21	60	178	10
0402	Paper	10,000	2	13	21	60	178	10
0603	Paper	5,000	2	13	21	60	178	10
0805	Paper	5,000	2	13	21	60	178	10
1206	Paper	5,000	2	13	21	60	178	10
1210	Paper	5,000	2	13	21	60	178	10
2010	Embossed	4,000	2	13	21	60	178	13.8
2512	Embossed	4,000	2	13	21	60	178	13.8

### **How To Order**

CRG	0603	F	10K
Common Part	Size	Tolerance	Resistance Value
	0201		1 ohm (1Ω) 1R0
	0402		
	0603		1K ohm (1000Ω) 1K0
CRG - Thick Film	0805	F - ±1%	
Chip Resistor	1206		100K ohm (100000Ω)
	1210		100K
	2010		
	2512		1M ohm (1000000Ω) 1M0