

General Information

Extended Product Type:	ZK10-PV
Product ID:	1SNK710063R0000
EAN:	3472599002739
Catalog Description:	ZK10-PV PI-Spring clamp Terminal Block - Feed-through - Grey
Long Description:	Specially designed for high voltage utility scale solar power plants: - Rated voltage of 1500 V DC IEC and 1000 V DC UL, - Pre-mounted end section with light grey color specific to this application, - Improved design with ribs to increase creepage distance, - Compact solution only 2 mm thicker than normal product, - Compatible with JB12 jumpers to interconnect multiple terminal blocks.

Ordering

Color:	Grey
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	12 mm
Product Net Height:	47.5 mm
Product Net Depth / Length:	82.5 mm
Product Net Weight:	29.86 g

Technical

Rated Cross-Section:	10 mm ²
Spacing:	12 mm
Connection Type:	PI Spring
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.5 ... 10 mm ² Spring Clamp / Rigid 1x 0.5 ... 16 mm ² Spring Clamp / With Insulated Ferrule 1x 0.5 ... 10 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.5 ... 10 mm ² Spring Clamp / With Twin Ferrule 2x 0.5 ... 4 mm ²
Gauge Type:	A6 & 5.1 mm Dia.
Rated Current (I_n):	Main Circuit 57 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 1200 A

Rated Voltage (U_r):	1000 V AC / 1500 V DC
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	1.8 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 1000 V
Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Rigid 1x 20 ... 6 AWG Spring Clamp / With Insulated Ferrule 1x 20 ... 8 AWG Spring Clamp / Without Insulated Ferrule 1x 20 ... 8 AWG
Connecting Capacity UL/CSA:	Stranded 6 AWG
Flammability According to UL94:	V0
Short-Circuit Current Rating (SCCR):	100 kA

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

CB Certificate:	1SND162011A0202
CSA Certificate:	1SND162014A0206
cUL Certificate:	1SND162012A0204
Declaration of Conformity - CE:	1SND225104U1001
EAC Certificate:	1SND162001A1100
Environmental Information:	1SND220072E1002
RoHS Information:	1SND230535F0201

Classifications

ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block

ETIM 6:

EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units: 20 piece

Package Level 1 Width: 86 mm

Package Level 1 Depth / Length: 250 mm

Package Level 1 Height: 51 mm

Package Level 1 Gross Weight: 0.617 kg

Package Level 1 EAN: 3472599002739

Package Level 2 Units: 240 piece


Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 400 mm

Package Level 2 Height: 200 mm

Package Level 3 Units: 11520 piece

Product Packing Type: Box

 300x200