

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNK Series

General Information

Extended Product Type:	ZS6-D1-RD
Product ID:	1SNK506214R0000
EAN:	3472595062140
Catalog Description:	ZS6-D1-RD Screw Clamp Terminal Block - Double Deck - Red
Long Description:	- Save space with double deck terminal blocks: 2 independent circuits connected in just 6 mm 0.236 in spacing, - Customize yourself the ZS6-D2 by soldering electronic components (up to 8.8 mm x 3.2 mm 0.346 x 0.125 in) in the existing linking bars punching, - Boost the performances: ZS6-D... with ES4-D2 end section is rated 1000 V DC IEC, perfectly adapted to solar applications.

Ordering

Color:	Red
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK161013D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	6 mm
Product Net Height:	70.4 mm
Product Net Depth / Length:	65.5 mm
Product Net Weight:	18.4 g

Technical

Rated Cross-Section:	6 mm ²
Spacing:	6 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	2

Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.2 ... 6 mm ² Screw Clamp / Flexible 2x 0.2 ... 2.5 mm ² Screw Clamp / Rigid 1x 0.2 ... 6 mm ² Screw Clamp / Rigid 2x 0.2 ... 2.5 mm ² Screw Clamp / With Insulated Ferrule 1x 0.22 ... 4 mm ² Screw Clamp / Without Insulated Ferrule 1x 0.22 ... 4 mm ² Screw Clamp / With Twin Ferrule 2x 0.22 ... 2.5 mm ²
Gauge Type:	A4-B3
Rated Current (I_n):	Main Circuit 40 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 720 A
Rated Voltage (U_r):	800 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2000 V
Pollution Degree:	3
Power Loss:	2.6 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	10.0 mm

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 300 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Flexible 1x 24 ... 10 AWG Screw Clamp / Flexible 2x 24 ... 14 AWG Screw Clamp / Rigid 1x 24 ... 10 AWG Screw Clamp / Rigid 2x 24 ... 14 AWG Screw Clamp / With Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / Without Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / With Twin Ferrule 2x 24 ... 14 AWG
Connecting Capacity UL/CSA:	Stranded 10 AWG
Flammability According to UL94:	V0
Short-Circuit Current Rating (SCCR):	100 kA

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant

RoHS Status:

Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

ATEX Certificate:	1SND162004A1708
BV Certificate:	1SND161073A0204
CSA Certificate:	1SND161070A0209
cUL Certificate:	1SND161040A0206
Declaration of Conformity - CE:	1SND225112U1004
DNV Certificate:	1SND161087A0202
EAC Certificate:	1SND161010A1100
Environmental Information:	1SND220071E1000
Instructions and Manuals:	1SNK160027C0201
RINA Certificate:	1SND161088A0200
RMRS Certificate:	1SND161008A1101

Classifications

Object Classification Code:	X
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	61 mm
Package Level 1 Depth / Length:	353 mm
Package Level 1 Height:	67 mm
Package Level 1 Gross Weight:	0.92 kg
Package Level 1 EAN:	3472595062140
Package Level 2 Units:	400 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	200 mm
Package Level 2 Height:	400 mm
Package Level 2 Gross Weight:	7.36 kg
Package Level 3 Units:	19200 piece
Product Packing Type:	Box

