

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Female Plugs

General Information

| | |
|-------------------------------|---|
| Extended Product Type: | CDS4-3 |
| Product ID: | 1SNK805728R0000 |
| EAN: | 3472598057280 |
| Catalog Description: | CDS4-3 Female Plug - 3 poles - Grey |
| Long Description: | - Create your own female plug assemblies without any special tools, easily snap together multiple plugs for optimal ergonomics and quick assembly, - Increase your flexibility: eliminate stock of pre-configured female plugs, easily add an extra plug in case of needed modification, - Reduce your stock of unitary plugs up to 30%: only two plug variants are required to compose your own subsets of plugs from 2 to 15 poles. |

Ordering

| | |
|--------------------------------|----------|
| Color: | Grey |
| Minimum Order Quantity: | 30 piece |
| Customs Tariff Number: | 85369010 |

Popular Downloads

| | |
|---|-----------------|
| Data Sheet, Technical Information: | 1SNK162052D0201 |
| Instructions and Manuals: | 1SNK160027C0205 |

Dimensions

| | |
|------------------------------------|---------|
| Product Net Width: | 5.2 mm |
| Product Net Height: | 22.4 mm |
| Product Net Depth / Length: | 39.4 mm |
| Product Net Weight: | 11.9 g |

Technical

| | |
|-----------------------------|-------------------|
| Rated Cross-Section: | 4 mm ² |
| Spacing: | 5.2 mm |
| Connection Type: | Screw clamp |
| Function: | Female Plugs |

| | |
|---|--|
| Connecting Capacity Main Circuit: | Screw Clamp / Flexible 1x 0.22 ... 4 mm ² Screw Clamp / Flexible 2x 0.22 ... 1.5 mm ² Screw Clamp / Rigid 1x 0.2 ... 4 mm ² Screw Clamp / Rigid 2x 0.2 ... 1.5 mm ² Screw Clamp / With Insulated Ferrule 1x 0.22 ... 2.5 mm ² Screw Clamp / Without Insulated Ferrule 1x 0.22 ... 4 mm ² Screw Clamp / With Twin Ferrule 2x 0.22 ... 1.5 mm ² |
| Gauge Type: | A3-B3 |
| Rated Current (I_n): | Main Circuit 29 A |
| Rated Short-time Withstand Current (I_{cw}): | for 1 s 480 A |
| Rated Voltage (U_r): | 800 V |
| Rated Impulse Withstand Voltage (U_{imp}): | 8000 V |
| Power Loss: | 1.5 W |
| Degree of Protection: | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| Insulation Material: | Polyamide |
| Mounting on DIN Rail: | G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715 |
| Wire Stripping Length: | 10.5 mm |
| Suitable For: | ZDS4-22 |

Technical UL/CSA

| | |
|---|---|
| Maximum Operating Voltage | Main Circuit 300 V |
| UL/CSA: | |
| Connecting Capacity Main Circuit | Screw Clamp / Rigid 1x 24 ... 10 AWG |
| UL/CSA: | Screw Clamp / Rigid 2x 24 ... 16 AWG Screw Clamp / With Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / Without Insulated Ferrule 1x 24 ... 10 AWG Screw Clamp / With Twin Ferrule 2x 24 ... 16 AWG |
| Connecting Capacity UL/CSA: | Stranded 10 AWG |

Environmental

| | |
|---------------------------------|-----------------------------------|
| Ambient Air Temperature: | Operation -55 ... +110 °C |
| RoHS Status: | Following EU Directive 2011/65/EU |

Certificates and Declarations (Document Number)

| | |
|-------------------------|-----------------|
| BV Certificate: | 1SND161073A0204 |
| CB Certificate: | 1SND164007A0200 |
| CSA Certificate: | 1SND164009A0200 |
| cUL Certificate: | 1SND164008A0200 |

| | |
|--|-----------------|
| Declaration of Conformity - CE: | 1SND225107U1000 |
| EAC Certificate: | 1SND161009A1100 |
| Environmental Information: | 1SND220092E1000 |
| Instructions and Manuals: | 1SNK160027C0205 |
| RoHS Information: | 1SND230537F0200 |

Classifications

| | |
|------------------------------------|----------------------------|
| Object Classification Code: | X |
| ETIM 4: | EC002638 - Cable connector |
| ETIM 5: | EC002638 - Cable connector |
| ETIM 6: | EC002638 - Cable connector |

Container Information

| | |
|--|---------------|
| Package Level 1 Units: | 30 piece |
| Package Level 1 Width: | 95 mm |
| Package Level 1 Depth / Length: | 205 mm |
| Package Level 1 Height: | 28 mm |
| Package Level 1 Gross Weight: | 0.381 kg |
| Package Level 1 EAN: | 3472598057280 |
| Package Level 2 Units: | 720 piece |
| Package Level 2 Width: | 300 mm |
| Package Level 2 Depth / Length: | 400 mm |
| Package Level 2 Height: | 200 mm |
| Package Level 3 Units: | 34560 piece |
| Product Packing Type: | Box |

